

SKINMATIC MH M63 PLUS / SW75

Article No.: 61791269

Wrench; Wrench width: 2.953in



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SKINMATIC®
Product type	Wrench
Delivery Unit	1

Electrical parameters

Product design

Wrench width	2.953 in
Material	Steel
Surface protection	Chrome-plated
for gland sizes	M 63 Plus
For cable gland material	Brass

Product features**Certifications and standards**

CE marking	No
VDE certified	No
TÜV certified	No

SKINMATIC® MH single wrench

Article No.	Name	Wrench width
61791267	SKINMATIC MH M50 / SW54	2.126 ir
61791268	SKINMATIC MH M63 / SW67	2.638 ir
61791269	SKINMATIC MH M63 PLUS / SW75	2.953 ir
61791286	SKINMATIC MH M75 / SW95	3.74 ir
61791287	SKINMATIC MH M90 / SW115	4.528 ir
61791288	SKINMATIC MH M110 / SW135	5.315 ir

V1.1