

**SILVYN® HCC 20 / 14.8X20.0 BK**

**Article No.:** 61793990

Parallel corrugated protective conduit; Inner diameter: 0.531in; Outer diameter: 0.787 in; Nominal size: 20; Polyamide; Halogen-free; UV-resistant



**CE**



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

**Technical Data**

**General information**

Brand	SILVYN®
Product type	Parallel corrugated protective conduit
Delivery Unit	50

---

**Electrical parameters****Product design**

With bending protection	No
Bending protection fixed installation	No
Flexibly installed bending protection	No
Slotted	No
Inner diameter	0.531 in
Outer diameter	0.787 in
Total length	1,968.504 in
Nominal size	20 "
EMC shielding	No
Material conduit	Polyamide
Conduit material, short form	PA 6
Conduit surface externally smooth	No
Smooth inner conduit surface	No
Colour description	black
RAL color	RAL 9005

**Product features**

For permanent bending	No
Suitable for EX-applications	No
Flame-retardant	Yes
Flame retardance according to	UL 94 HB
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

**Certifications and standards**

CE marking	Yes
EAC certified	Not required

---

EAC certification number	Отказное письмо № 505
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
DNV-certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

---

**SILVYN® HCC**

Article No.	Name	Inner diameter	Outer diameter	Nominal size	Total length	Colour description	Delivery Unit
61793970	SILVYN® HCC 12 / 9.8X13.0 BK	0.35 in	0.508 in	12 "	1,968.504 in	black	50
61793980	SILVYN® HCC 16 / 11.8X16.0 BK	0.437 in	0.63 in	16 "	1,968.504 in	black	50
61793990	SILVYN® HCC 20 / 14.8X20.0 BK	0.531 in	0.787 in	20 "	1,968.504 in	black	50
61794000	SILVYN® HCC 25 / 19.1X25.0 BK	0.697 in	0.984 in	25 "	1,968.504 in	black	50
61794010	SILVYN® HCC 32 / 24.3X32.0 BK	0.957 in	1.26 in	32 "	1,968.504 in	black	25
61794020	SILVYN® HCC 40 / 30.2X40.0 BK	1.189 in	1.575 in	40 "	984.252 in	black	25
61794030	SILVYN® HCC 50 / 40.1X50.0 BK	1.579 in	1.969 in	50 "	984.252 in	black	25
61794035	SILVYN® HCC 63 / 52.5X63.0 BK	2.067 in	2.48 in	63 "	984.252 in	black	25

V1.1