

**ASSORTMENT BOX AHI II**

**Article No.:** 61794730

Conductor end sleeve; Suitable crimping insert: PEW 12.090; orange; Electrolytic copper Tin-plated



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

**Remarks**

Trade product, not a LAPP product.

**Technical Data**

**General information**

Product type	Conductor end sleeve
Type of packaging	Assortment box

Delivery Unit	1
Suitable crimping insert	PEW 12.090

### Electrical parameters

#### Product design

For cross-section (min.)	0.5 mm <sup>2</sup>
For cross-section (max.)	2.5 mm <sup>2</sup>
Connector material	Electrolytic copper
Insulation material	Polypropylene
Surface protection	Tin-plated
Colour description	orange
cable lug design	Conductor end sleeve

#### Product features

Flame-retardant	Yes
Flame retardance according to	UL 94 HB
UV-resistant	No
Chemical resistant	Yes
corrosion resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

#### Certifications and standards

CE marking	No
EAC certified	Not required
EAC certification number	Отказное письмо № 39
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No

---

CSA certified	No
VDE certified	No

---

**assorted boxes end sleeves**

Article No.	Name	Suitable crimping insert	For cross-section (min.)	For cross-section (max.)	Delivery Unit
61794720	ASSORTMENT BOX AHI I	PEW 12.090	0.25 mm <sup>2</sup>	1 mm <sup>2</sup>	1
61794730	ASSORTMENT BOX AHI II	PEW 12.090	0.5 mm <sup>2</sup>	2.5 mm <sup>2</sup>	1
61794740	ASSORTMENT BOX AHI III	PEW 12.090,PEW 12.091	4 mm <sup>2</sup>	16 mm <sup>2</sup>	1
61802040	ASSORTMENT BOX DIN I	PEW 12.090	0.25 mm <sup>2</sup>	1 mm <sup>2</sup>	1
61802041	ASSORTMENT BOX DIN II	PEW 12.090	0.5 mm <sup>2</sup>	2.5 mm <sup>2</sup>	1
61802042	ASSORTMENT BOX DIN III	PEW 12.090,PEW 12.091	4 mm <sup>2</sup>	16 mm <sup>2</sup>	1
61802046	ASSORTMENT BOX TWIN	PEW 12.090-6	0.75 mm <sup>2</sup>	2.5 mm <sup>2</sup>	1

V1.1