

TUBE CABLE LUGS KR 10/5**Article No.:** 61796631

Cable lug; Suitable crimping insert: B7B8; for cross-section: 10mm²; M5; Electrolytic copper

**Details****Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data
General information

Product type	Cable lug
Type of packaging	Cardboard packaging
Delivery Unit	100
Suitable crimping insert	B 7 B 8
Industry segment	Rolling Stock

Electrical parameters

applicable up to voltage	48,000 V
--------------------------	----------

Product design

Total length	1.142 in
Screw hole size	M5
for cross-section	10 mm ²
Connector material	Electrolytic copper
Surface protection	Tin-plated
cable lug design	Tube cable lug

Product features

Short term temperature max.	140 °C
Flame-retardant	Yes
UV-resistant	Yes
Chemical resistant	Yes
corrosion resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	Yes
EAC certified	Not required
EAC certification number	Отказное письмо № 39
UL recognized	No
UL listed	Yes
UL certification	according to UL 486A/486B (e-file number: E205350)
cUR recognized	No
cUL listed	Yes
cUL certification	according to CSA C22.2 No. 65 (e-file number: E205350)
CSA certified	No
VDE certified	No
DNV-certified	No

Tube cable lugs KR

Article No.	Name	Suitable crimping insert	for cross-section	Screw hole size	Delivery Unit
61796480	TUBE CABLE LUGS KR 0.75/3		0.75 mm ²	M3	100
61796500	TUBE CABLE LUGS KR 1.5/3		1.5 mm ²	M3	100
61796510	TUBE CABLE LUGS KR 1.5/4		1.5 mm ²	M4	100
61796520	TUBE CABLE LUGS KR 1.5/5		1.5 mm ²	M5	100
61796530	TUBE CABLE LUGS KR 2.5/3		2.5 mm ²	M3	100
61796540	TUBE CABLE LUGS KR 2.5/4		2.5 mm ²	M4	100
61796550	TUBE CABLE LUGS KR 2.5/5		2.5 mm ²	M5	100
61796560	TUBE CABLE LUGS KR 2.5/6		2.5 mm ²	M6	100
61796570	TUBE CABLE LUGS KR 4/4		4 mm ²	M4	100
61796580	TUBE CABLE LUGS KR 4/5		4 mm ²	M5	100
61796590	TUBE CABLE LUGS KR 4/6		4 mm ²	M6	100
61796600	TUBE CABLE LUGS KR 6/4		6 mm ²	M4	100
61796610	TUBE CABLE LUGS KR 6/5		6 mm ²	M5	100
61796620	TUBE CABLE LUGS KR 6/6		6 mm ²	M6	100
61796630	TUBE CABLE LUGS KR 6/8		6 mm ²	M8	100
61796631	TUBE CABLE LUGS KR 10/5	B 7,B 8	10 mm ²	M5	100
61796632	TUBE CABLE LUGS KR 10/6	B 7,B 8	10 mm ²	M6	100
61796633	TUBE CABLE LUGS KR 10/8	B 7,B 8	10 mm ²	M8	100

V1.1