

TUBE CABLE LUGS KRT 25/8

Article No.: 61796750

Cable lug; Suitable crimping insert: B10; For cross-section: 25mm²; M8; Electrolytic copper



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data

General information

Product type	Cable lug
Type of packaging	Cardboard packaging
Delivery Unit	100
Suitable crimping insert	B 10
Industry segment	Agricultural & Farm Machinery Rolling Stock

Electrical parameters

applicable up to voltage	48,000 V
--------------------------	----------

Product design

Total length	1.693 in
Screw hole size	M8
for cross-section	25 mm ²
Connector material	Electrolytic copper
Surface protection	Tin-plated
cable lug design	Tube cable lug

Product features

Short term temperature max.	140 °C
Flame-retardant	Yes
UV-resistant	Yes
Chemical resistant	Yes
corrosion resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	Yes
EAC certified	Not required
EAC certification number	Отказное письмо № 39

UL recognized	No
UL listed	Yes
UL certification	according to UL 486A/486B (e-file number: E205350)
cUR recognized	No
cUL listed	Yes
cUL certification	according to CSA C22.2 No. 65 (e-file number: E205350)
CSA certified	No
VDE certified	No
DNV-certified	Yes
DNV certificate number	TAE00002U2

Tube cable lugs KRT

Article No.	Name	Suitable crimping insert	for cross-section	Screw hole size	Delivery Unit
61796640	TUBE CABLE LUGS KRT 10/5	B 7	10 mm ²	M5	100
61796650	TUBE CABLE LUGS KRT 10/6	B 7	10 mm ²	M6	100
61796660	TUBE CABLE LUGS KRT 10/8	B 7	10 mm ²	M8	100
61796670	TUBE CABLE LUGS KRT 10/10	B 7	10 mm ²	M10	100
61796680	TUBE CABLE LUGS KRT 10/12	B 7	10 mm ²	M12	100
61796690	TUBE CABLE LUGS KRT 16/5	B 8,5	16 mm ²	M5	100
61796700	TUBE CABLE LUGS KRT 16/6	B 8,5	16 mm ²	M6	100
61796710	TUBE CABLE LUGS KRT 16/8	B 8,5	16 mm ²	M8	100
61796720	TUBE CABLE LUGS KRT 16/10	B 8,5	16 mm ²	M10	100
61796730	TUBE CABLE LUGS KRT 16/12	B 8,5	16 mm ²	M12	100
61796740	TUBE CABLE LUGS KRT 25/6	B 10	25 mm ²	M6	100
61796750	TUBE CABLE LUGS KRT 25/8	B 10	25 mm ²	M8	100
61796760	TUBE CABLE LUGS KRT 25/10	B 10	25 mm ²	M10	100
61796770	TUBE CABLE LUGS KRT 25/12	B 10	25 mm ²	M12	100
61796780	TUBE CABLE LUGS KRT 35/6	B 12	35 mm ²	M6	100
61796790	TUBE CABLE LUGS KRT 35/8	B 12	35 mm ²	M8	100
61796800	TUBE CABLE LUGS KRT 35/10	B 12	35 mm ²	M10	100
61796810	TUBE CABLE LUGS KRT 35/12	B 12	35 mm ²	M12	50
61796820	TUBE CABLE LUGS KRT 50/6	B 14	50 mm ²	M6	50
61796830	TUBE CABLE LUGS KRT 50/8	B 14	50 mm ²	M8	50
61796840	TUBE CABLE LUGS KRT 50/10	B 14	50 mm ²	M10	50
61796850	TUBE CABLE LUGS KRT 50/12	B 14	50 mm ²	M12	50
61796860	TUBE CABLE LUGS KRT 70/8	B 16	70 mm ²	M8	50
61796870	TUBE CABLE LUGS KRT 70/10	B 16	70 mm ²	M10	50
61796880	TUBE CABLE LUGS KRT 70/12	B 16	70 mm ²	M12	50
61796890	TUBE CABLE LUGS KRT 95/8	B 18	95 mm ²	M8	50
61796900	TUBE CABLE LUGS KRT 95/10	B 18	95 mm ²	M10	50
61796910	TUBE CABLE LUGS KRT 95/12	B 18	95 mm ²	M12	50
61796920	TUBE CABLE LUGS KRT 95/16	B 18	95 mm ²	M16	50
61796930	TUBE CABLE LUGS KRT 120/10	B 19	120 mm ²	M10	50

Article No.	Name	Suitable crimping insert	for cross-section	Screw hole size	Delivery Unit
61796940	TUBE CABLE LUGS KRT 120/12	B 19	120 mm ²	M12	50
61796950	TUBE CABLE LUGS KRT 120/16	B 19	120 mm ²	M16	50
61796960	TUBE CABLE LUGS KRT 150/12	B 22	150 mm ²	M12	25
61796990	TUBE CABLE LUGS KRT 185/12	B 24	185 mm ²	M12	25
61797000	TUBE CABLE LUGS KRT 185/16	B 24	185 mm ²	M16	25
61797020	TUBE CABLE LUGS KRT 240/12	13 B 26	240 mm ²	M12	25
61797030	TUBE CABLE LUGS KRT 240/16	13 B 26	240 mm ²	M16	25

V1.1