

TUBE CABLE LUGS KRT 50/8

Article No.: 61796830

Cable lug; Suitable crimping insert: B14; For cross-section: 50mm²; M8; Electrolytic copper



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data

General information

| | |
|--------------------------|--|
| Product type | Cable lug |
| Type of packaging | Cardboard packaging |
| Delivery Unit | 50 |
| Suitable crimping insert | B 14 |
| Industry segment | Agricultural & Farm Machinery Rolling Stock |

Electrical parameters

| | |
|--------------------------|----------|
| applicable up to voltage | 48,000 V |
|--------------------------|----------|

Product design

| | |
|--------------------|---------------------|
| Total length | 2.087 in |
| Screw hole size | M8 |
| for cross-section | 50 mm ² |
| Connector material | Electrolytic copper |
| Surface protection | Tin-plated |
| cable lug design | Tube cable lug |

Product features

| | |
|-----------------------------|--------|
| Short term temperature max. | 140 °C |
| Flame-retardant | Yes |
| UV-resistant | Yes |
| Chemical resistant | Yes |
| corrosion resistant | Yes |
| Halogenfree | Yes |
| Oil resistant | Yes |

Certifications and standards

| | |
|--------------------------|----------------------|
| CE marking | Yes |
| EAC certified | Not required |
| EAC certification number | Отказное письмо № 39 |

| | |
|------------------------|--|
| UL recognized | No |
| UL listed | Yes |
| UL certification | according to UL 486A/486B (e-file number: E205350) |
| cUR recognized | No |
| cUL listed | Yes |
| cUL certification | according to CSA C22.2 No. 65 (e-file number: E205350) |
| CSA certified | No |
| VDE certified | No |
| DNV-certified | Yes |
| DNV certificate number | TAE00002U2 |

Tube cable lugs KRT

| Article No. | Name | Suitable crimping insert | for cross-section | Screw hole size | Delivery Unit |
|-------------|----------------------------|--------------------------|---------------------|-----------------|---------------|
| 61796640 | TUBE CABLE LUGS KRT 10/5 | B 7 | 10 mm ² | M5 | 100 |
| 61796650 | TUBE CABLE LUGS KRT 10/6 | B 7 | 10 mm ² | M6 | 100 |
| 61796660 | TUBE CABLE LUGS KRT 10/8 | B 7 | 10 mm ² | M8 | 100 |
| 61796670 | TUBE CABLE LUGS KRT 10/10 | B 7 | 10 mm ² | M10 | 100 |
| 61796680 | TUBE CABLE LUGS KRT 10/12 | B 7 | 10 mm ² | M12 | 100 |
| 61796690 | TUBE CABLE LUGS KRT 16/5 | B 8,5 | 16 mm ² | M5 | 100 |
| 61796700 | TUBE CABLE LUGS KRT 16/6 | B 8,5 | 16 mm ² | M6 | 100 |
| 61796710 | TUBE CABLE LUGS KRT 16/8 | B 8,5 | 16 mm ² | M8 | 100 |
| 61796720 | TUBE CABLE LUGS KRT 16/10 | B 8,5 | 16 mm ² | M10 | 100 |
| 61796730 | TUBE CABLE LUGS KRT 16/12 | B 8,5 | 16 mm ² | M12 | 100 |
| 61796740 | TUBE CABLE LUGS KRT 25/6 | B 10 | 25 mm ² | M6 | 100 |
| 61796750 | TUBE CABLE LUGS KRT 25/8 | B 10 | 25 mm ² | M8 | 100 |
| 61796760 | TUBE CABLE LUGS KRT 25/10 | B 10 | 25 mm ² | M10 | 100 |
| 61796770 | TUBE CABLE LUGS KRT 25/12 | B 10 | 25 mm ² | M12 | 100 |
| 61796780 | TUBE CABLE LUGS KRT 35/6 | B 12 | 35 mm ² | M6 | 100 |
| 61796790 | TUBE CABLE LUGS KRT 35/8 | B 12 | 35 mm ² | M8 | 100 |
| 61796800 | TUBE CABLE LUGS KRT 35/10 | B 12 | 35 mm ² | M10 | 100 |
| 61796810 | TUBE CABLE LUGS KRT 35/12 | B 12 | 35 mm ² | M12 | 50 |
| 61796820 | TUBE CABLE LUGS KRT 50/6 | B 14 | 50 mm ² | M6 | 50 |
| 61796830 | TUBE CABLE LUGS KRT 50/8 | B 14 | 50 mm ² | M8 | 50 |
| 61796840 | TUBE CABLE LUGS KRT 50/10 | B 14 | 50 mm ² | M10 | 50 |
| 61796850 | TUBE CABLE LUGS KRT 50/12 | B 14 | 50 mm ² | M12 | 50 |
| 61796860 | TUBE CABLE LUGS KRT 70/8 | B 16 | 70 mm ² | M8 | 50 |
| 61796870 | TUBE CABLE LUGS KRT 70/10 | B 16 | 70 mm ² | M10 | 50 |
| 61796880 | TUBE CABLE LUGS KRT 70/12 | B 16 | 70 mm ² | M12 | 50 |
| 61796890 | TUBE CABLE LUGS KRT 95/8 | B 18 | 95 mm ² | M8 | 50 |
| 61796900 | TUBE CABLE LUGS KRT 95/10 | B 18 | 95 mm ² | M10 | 50 |
| 61796910 | TUBE CABLE LUGS KRT 95/12 | B 18 | 95 mm ² | M12 | 50 |
| 61796920 | TUBE CABLE LUGS KRT 95/16 | B 18 | 95 mm ² | M16 | 50 |
| 61796930 | TUBE CABLE LUGS KRT 120/10 | B 19 | 120 mm ² | M10 | 50 |

| Article No. | Name | Suitable crimping insert | for cross-section | Screw hole size | Delivery Unit |
|-------------|----------------------------|--------------------------|---------------------|-----------------|---------------|
| 61796940 | TUBE CABLE LUGS KRT 120/12 | B 19 | 120 mm ² | M12 | 50 |
| 61796950 | TUBE CABLE LUGS KRT 120/16 | B 19 | 120 mm ² | M16 | 50 |
| 61796960 | TUBE CABLE LUGS KRT 150/12 | B 22 | 150 mm ² | M12 | 25 |
| 61796990 | TUBE CABLE LUGS KRT 185/12 | B 24 | 185 mm ² | M12 | 25 |
| 61797000 | TUBE CABLE LUGS KRT 185/16 | B 24 | 185 mm ² | M16 | 25 |
| 61797020 | TUBE CABLE LUGS KRT 240/12 | 13 B 26 | 240 mm ² | M12 | 25 |
| 61797030 | TUBE CABLE LUGS KRT 240/16 | 13 B 26 | 240 mm ² | M16 | 25 |

V1.1