

SILVYN® LTP-E 32

Article No.: 61802306

Screw-in sleeve; Nominal size: 32; Suitable for protective cable conduit size: 1; Brass;



CE



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SILVYN®
Product type	Screw-in sleeve
Delivery with lock nut	No
Including o-ring	No

Delivery Unit	10
Mounting method	screw
Industry segment	Rolling Stock

Electrical parameters

Product design

suitable for protective conduit size	1
With bending protection	No
Bending protection fixed installation	No
Flexibly installed bending protection	No
Slotted	No
Divisible conduit gland	No
Rotatable thread	No
Inner diameter	0.969 in
Outer diameter	1.378 in
Total length	0.945 in
Clear width	0.969 in
Nominal size	32 "
Lockable (two-part)	No
EMC shielding	No
Gland body material	Brass
Material fitting body shortname	CuZn
Surface protection	Nickel-plated

Product features

Suitable for EX-applications	No
Flame-retardant	No
UV-resistant	Yes
Chemical resistant	Yes
Acid-resistant	No
Halogenfree	Yes

Oil resistant	Yes
Impact proof	No
Vibration protection	Yes
Strain relief	No

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
Product standard according to IEC	IEC 61386-23
GGVS certified	No
DNV-certified	No
Tested for fire protection for railway vehicles	No
Ecolab certified	No
NSF certified	No
FDA certified	No
EHEDG certified	No

SILVYN® LTP-E

Article No.	Name	Nominal size	suitable for protective conduit size	Delivery Unit
61802302	SILVYN® LTP-E 16	16 "	3/8	10
61802303	SILVYN® LTP-E 20	20 "	1/2	10
61802304	SILVYN® LTP-E 50	50 "	1.5	4
61802305	SILVYN® LTP-E 25	25 "	3/4	10
61802306	SILVYN® LTP-E 32	32 "	1	10
61802308	SILVYN® LTP-E 63	63 "	2	1

V1.1