

SILVYN® US-EDU-AS 10**Article No.:** 61802480

End sleeve; Nominal size: 10; Suitable for protective cable conduit size: 10;

**Details****Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SILVYN®
Product type	End sleeve
Type of packaging	Bag
Delivery Unit	50
Mounting method	screw

Electrical parameters**Product design**

suitable for protective conduit size	10
With bending protection	No
Clear width	0.236 in
Nominal size	10 "
EMC shielding	No
Gland body material	Brass
Material fitting body shortname	CuZn

Product features

Suitable for EX-applications	No
Flame-retardant	Yes
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	No
UL recognized	No
UL listed	No

cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Ecolab certified	No
NSF certified	No
FDA certified	No
EHEDG certified	No

SILVYN® US-EDU-AS

Article No.	Name	Nominal size	Delivery Unit
61802480	SILVYN® US-EDU-AS 10	10 "	50
61802490	SILVYN® US-EDU-AS 14	14 "	50
61802500	SILVYN® US-EDU-AS 17	17 "	50
61802510	SILVYN® US-EDU-AS 19	19 "	50
61802520	SILVYN® US-EDU-AS 21	21 "	50
61802530	SILVYN® US-EDU-AS 27	27 "	25
61802540	SILVYN® US-EDU-AS 36	36 "	25
61802550	SILVYN® US-EDU-AS 45	45 "	20
61802570	SILVYN® US-EDU-AS 56	56 "	10

V1.1