

SILVYN® US-FPS-EDU-AS 56

Article No.: 61802588

End sleeve; Nominal size: 56; Suitable for protective cable conduit size: 56; Brass;



CE



Details

Notes

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Remarks

Technical Data

General information

Brand	SILVYN®
Product type	End sleeve
Scope of delivery	including O-ring
Delivery with lock nut	No

Including o-ring	No
Type of packaging	Bag
Delivery Unit	10
Mounting method	screw

Electrical parameters

Product design

suitable for protective conduit size	56
With bending protection	No
Conduit gland design	Straight
Nominal size	56 "
EMC shielding	No
Body material	Brass
Body material, short form	CuZn

Product features

Suitable for EX-applications	No
Flame-retardant	Yes
UV-resistant	Yes
Chemical resistant	Yes
Acid-resistant	No
Halogenfree	Yes
Oil resistant	Yes
Impact proof	No
Vibration protection	Yes

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No

cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Tested for fire protection for railway vehicles	No
Ecolab certified	No
NSF certified	No
FDA certified	No
EHEDG certified	No

SILVYN® US-FPS-EDU-AS

Article No.	Name	Nominal size	Delivery Unit
61802584	SILVYN® US-FPS-EDU-AS 21	21 "	50
61802588	SILVYN® US-FPS-EDU-AS 56	56 "	10

V1.1