

TUBE CABLE LUGS KRF 16/8

Article No.: 61803030

Cable lug; Suitable crimping insert: B9; For cross-section: 16mm²; M8; Electrolytic copper



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data

General information

Product type	Cable lug
Type of packaging	Cardboard packaging
Delivery Unit	100
Suitable crimping insert	B 9
Industry segment	Agricultural & Farm Machinery Rolling Stock

Electrical parameters

applicable up to voltage	48,000 V
--------------------------	----------

Product design

Total length	1.339 in
Screw hole size	M8
for cross-section	16 mm ²
Connector material	Electrolytic copper
Surface protection	Tin-plated
cable lug design	Tube cable lug

Product features

Short term temperature max.	140 °C
Flame-retardant	Yes
UV-resistant	Yes
Chemical resistant	Yes
corrosion resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	Yes
EAC certified	Not required
EAC certification number	Отказное письмо № 39

UL recognized	No
UL listed	Yes
UL certification	according to UL 486A/486B (e-file number: E205350)
cUR recognized	No
cUL listed	Yes
cUL certification	according to CSA C22.2 No. 65 (e-file number: E205350)
CSA certified	No
VDE certified	No
DNV-certified	Yes
DNV certificate number	TAE00002U2

Tube cable lugs KRF

Article No.	Name	Suitable crimping insert	for cross-section	Screw hole size	Delivery Unit
61803020	TUBE CABLE LUGS KRF 16/6	B 9	16 mm ²	M6	100
61803030	TUBE CABLE LUGS KRF 16/8	B 9	16 mm ²	M8	100
61803040	TUBE CABLE LUGS KRF 16/10	B 9	16 mm ²	M10	100
61803050	TUBE CABLE LUGS KRF 16/12	B 9	16 mm ²	M12	100
61803060	TUBE CABLE LUGS KRF 25/6	B 11	25 mm ²	M6	100
61803070	TUBE CABLE LUGS KRF 25/8	B 11	25 mm ²	M8	100
61803080	TUBE CABLE LUGS KRF 25/10	B 11	25 mm ²	M10	100
61803090	TUBE CABLE LUGS KRF 25/12	B 11	25 mm ²	M12	100
61803110	TUBE CABLE LUGS KRF 35/6	B 13	35 mm ²	M6	100
61803120	TUBE CABLE LUGS KRF 35/8	B 13	35 mm ²	M8	100
61803130	TUBE CABLE LUGS KRF 35/10	B 13	35 mm ²	M10	100
61803140	TUBE CABLE LUGS KRF 35/12	B 13	35 mm ²	M12	100
61803160	TUBE CABLE LUGS KRF 50/8	B 14,5	50 mm ²	M8	100
61803170	TUBE CABLE LUGS KRF 50/10	B 14,5	50 mm ²	M10	100
61803180	TUBE CABLE LUGS KRF 50/12	B 14,5	50 mm ²	M12	100
61803200	TUBE CABLE LUGS KRF 70/8	B 17	70 mm ²	M8	50
61803210	TUBE CABLE LUGS KRF 70/10	B 17	70 mm ²	M10	50
61803220	TUBE CABLE LUGS KRF 70/12	B 17	70 mm ²	M12	50
61803230	TUBE CABLE LUGS KRF 70/16	B 17	70 mm ²	M16	50
61803240	TUBE CABLE LUGS KRF 95/10	B 20	95 mm ²	M10	50
61803250	TUBE CABLE LUGS KRF 95/12	B 20	95 mm ²	M12	50
61803260	TUBE CABLE LUGS KRF 95/16	B 20	95 mm ²	M16	50
61803270	TUBE CABLE LUGS KRF 120/10	B 22	120 mm ²	M10	25
61803280	TUBE CABLE LUGS KRF 120/12	B 22	120 mm ²	M12	25
61803290	TUBE CABLE LUGS KRF 120/16	B 22	120 mm ²	M16	25
61803300	TUBE CABLE LUGS KRF 150/12	B 25,13 B 25	150 mm ²	M12	25
61803310	TUBE CABLE LUGS KRF 150/16	B 25,13 B 25	150 mm ²	M16	25
61803330	TUBE CABLE LUGS KRF 185/12	13 B 27	185 mm ²	M12	20
61803360	TUBE CABLE LUGS KRF 240/12	13 B 30	240 mm ²	M12	10
61803370	TUBE CABLE LUGS KRF A 240/16	13 B 30	240 mm ²	M16	10

Article No.	Name	Suitable crimping insert	for cross-section	Screw hole size	Delivery Unit
61803380	TUBE CABLE LUGS KRF 240/20	13 B 30	240 mm ²	M20	10
61803390	TUBE CABLE LUGS KRF 300/16	13 B 32	300 mm ²	M16	10

V1.1