

**SILVYN® SPLIT GMP-M 50X1.5 LOCKNUT**

**Article No.:** 61806692

Lock nut; M 50; black; Polyamide; Halogen-free; UV-resistant



**CE**



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

**Technical Data**

**General information**

Brand	SILVYN®
Product type	Lock nut
Type of packaging	Bag

---

Delivery Unit	25
Mounting method	screw

---

**Electrical parameters****Product design**

Divisible conduit gland	Yes
Overall width	2.717 in
Overall height	0.591 in
Thread size	M 50
Pitch of thread	1,5
Thread standard	DIN EN 60423
Body material	Polyamide
Body material, short form	PA
Colour description	black
RAL color	RAL 9005

---

**Product features**

Suitable for EX-applications	No
Flame-retardant	Yes
Flame retardance according to	UL 94 V-2
UV-resistant	Yes
Chemical resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

---

**Certifications and standards**

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No

---

---

cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

---

---

**SILVYN® SPLIT GMP-M**

Article No.	Name	Thread size	Colour description	Delivery Unit
61806687	SILVYN® SPLIT GMP-M 20X1.5 LOCKNUT	M 20	black	100
61806688	SILVYN® SPLIT COV-M 25X1.5 LOCKNUT	M 25	black	50
61806689	SILVYN® SPLIT COV-M 32X1.5 LOCKNUT	M 32	black	50
61806691	SILVYN® SPLIT COV-M 40X1.5 LOCKNUT	M 40	black	25
61806692	SILVYN® SPLIT GMP-M 50X1.5 LOCKNUT	M 50	black	25

V1.1