

SILVYN® US-MS-DR 19

Article No.: 61808180

Add-on; Nominal size: 19; Brass; Halogen-free



Details

Notes

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Remarks

Technical Data

General information

Brand	SILVYN®
Product type	Add-on
Type of packaging	Bag
Delivery Unit	50
Mounting method	push on

Electrical parameters**Product design**

Inner diameter	0.756 in
Overall width	0.906 in
Overall height	0.236 in
Nominal size	19 "
EMC shielding	No
Gland body material	Brass
Material fitting body shortname	CuZn

Product features

Suitable for EX-applications	No
Flame-retardant	Yes
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	No
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
DNV-certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

SILVYN® US-MS-DR

Article No.	Name	Nominal size	Delivery Unit
61808168	SILVYN® US-MS-DR 10	10 "	50
61808169	SILVYN® US-MS-DR 14	14 "	50
61808170	SILVYN® US-MS-DR 17	17 "	50
61808180	SILVYN® US-MS-DR 19	19 "	50
61808190	SILVYN® US-MS-DR 21	21 "	50
61808200	SILVYN® US-MS-DR 27	27 "	25
61808201	SILVYN® US-MS-DR 36	36 "	25
61808202	SILVYN® US-MS-DR 45	45 "	20
61808204	SILVYN® US-MS-DR 56	56 "	10

V1.1