

CABLE TIES TY-FAST® 100-18X-M BK**Article No.:** 61810460

Cable ties; Cable tie width: 0.094in; Total length: 112mm; black; Polyamide; Halogen-free; UV-resistant

**Details****Notes**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data

General information

Product type	Cable ties
Delivery Unit	1,000
suitable tools	TY GUN ERG 50 cable tie pliers
Industry segment	Solar

Electrical parameters
Product design

Total length	4.409 in
for bundling diameter (max.)	0.984 in
Material	Polyamide
Cable tie width	0.094 in
Colour description	black

Product features

Flame-retardant	Yes
Flame retardance according to	UL 94 V-2
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	No
UL recognized	Yes
UL AWM certification	according to UL 1565 (e-file number: E49405) according to UL 62275 (e-file number: E49405)
UL listed	No
cUR recognized	Yes

cUR certification	according to CSA C22.2 No. 62275 (e-file number: E49405) according to CSA C22.2 No. 18.5 (e-file number: E49405)
cUL listed	No
CSA certified	No
VDE certified	No
DNV-certified	No
Ecolab certified	No

Ty-Fast® Cable ties

Article No.	Name	for bundling diameter (min.)	for bundling diameter (max.)	Cable tie width	Total length	Colour description	Delivery Unit
61810350	CABLE TIES TY-FAST® 100-18-M NR		0.984 in	0.094 in	4.409 in	natural	1,000
61810360	CABLE TIES TY-FAST® 125-18-M NR		1.26 in	0.094 in	5.354 in	natural	1,000
61810380	CABLE TIES TY-FAST® 125-40 NR		1.26 in	0.142 in	5.551 in	natural	1,000
61810390	CABLE TIES TY-FAST® 200-40-C NR		1.969 in	0.142 in	8.071 in	natural	100
61810400	CABLE TIES TY-FAST® 300-40 NR		2.992 in	0.142 in	11.417 in	natural	1,000
61810410	CABLE TIES TY-FAST® 175-50 NR		1.732 in	0.181 in	7.323 in	natural	1,000
61810420	CABLE TIES TY-FAST® 300-50 NR		2.992 in	0.181 in	11.457 in	natural	1,000
61810430	CABLE TIES TY-FAST® 400-50 NR		4.016 in	0.181 in	14.409 in	natural	1,000
61810450	CABLE TIES TY-FAST® 400-120 NR		4.016 in	0.299 in	14.764 in	natural	500
61810460	CABLE TIES TY-FAST® 100-18X-M BK		0.984 in	0.094 in	4.409 in	black	1,000
61810470	CABLE TIES TY-FAST® 125-18X-M BK		1.26 in	0.094 in	5.354 in	black	1,000
61810490	CABLE TIES TY-FAST® 125-40X BK		1.26 in	0.142 in	5.551 in	black	1,000
61810500	CABLE TIES TY-FAST® 200-40X-M BK		1.969 in	0.142 in	8.071 in	black	1,000
61810510	CABLE TIES TY-FAST® 300-40X BK		2.992 in	0.142 in	11.417 in	black	1,000
61810520	CABLE TIES TY-FAST® 175-50X BK		1.732 in	0.181 in	7.323 in	black	1,000
61810530	CABLE TIES TY-FAST® 300-50X BK		2.992 in	0.181 in	11.457 in	black	1,000
61810540	CABLE TIES TY-FAST® 400-50X BK		4.016 in	0.181 in	14.409 in	black	1,000
61810550	CABLE TIES TY-FAST® 200-120X-D BK		1.969 in	0.299 in	8.622 in	black	500
61810560	CABLE TIES TY-FAST® 400-120X BK		4.016 in	0.299 in	14.764 in	black	500

V1.1