

SILVYN® KLICK-D 10 / 13 GY

Article No.: 61811200

Mounting bracket; Nominal size: 10/13; Polyamide



Details

Notes

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Remarks

Technical Data

General information

Brand	SILVYN®
Product type	Mounting bracket
Delivery with lock nut	No
Including o-ring	No
Type of packaging	Bag
Delivery Unit	100

Electrical parameters**Product design**

Overall width	0.787 in
Overall height	0.197 in
Nominal size	10/13 "
Body material	Polyamide
Body material, short form	PA
Colour description	gray

Product features

Suitable for EX-applications	No
Flame-retardant	Yes
Flame retardance according to	UL 94 HB
UV-resistant	No
Chemical resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	No
EHEDG certified	No

SILVYN® KLICK-D

Article No.	Name	Nominal size	Overall width	Colour description	Delivery Unit
61811200	SILVYN® KLICK-D 10 / 13 GY	10/13 "	0.787 in	gray	100
61811210	SILVYN® KLICK-D 21 GY	18/21 "	1.102 in	gray	50
61811220	SILVYN® KLICK-D 28 GY	28 "	1.378 in	gray	50
61811230	SILVYN® KLICK-D 34 GY	34 "	1.654 in	gray	30
61811240	SILVYN® KLICK-D 42 GY	42 "	2.126 in	gray	20
61811250	SILVYN® KLICK-D 54 GY	54 "	2.657 in	gray	20
61811260	SILVYN® KLICK-D 16 GY	16 "	0.866 in	gray	50

V1.1