

SPARE TOOL CAT 20 / 25 CABLE EATER**Article No.:** 61830360

Cable entry tool; 0.669in - 0.984in; orange

**Details****Notes**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data**General information**

Product type	Cable entry tool
Delivery Unit	1

Electrical parameters

Product design

for bundling diameter (min.)	0.669 in
------------------------------	----------

for bundling diameter (max.)	0.984 in
------------------------------	----------

Colour description	orange
--------------------	--------

Product features

Flame-retardant	No
-----------------	----

Halogenfree	No
-------------	----

Oil resistant	No
---------------	----

Certifications and standards

Spare tool Cable-Eater

Article No.	Name	for bundling diameter (min.)	for bundling diameter (max.)	Colour description
61830340	SPARE TOOL CAT 8 CABLE EATER	0.236 in	0.354 in	orange
61830350	SPARE TOOL CAT 15 CABLE EATER	0.394 in	0.63 in	orange
61830360	SPARE TOOL CAT 20 / 25 CABLE EATER	0.669 in	0.984 in	orange

V1.1