

RING CABLE LUGS L-RB 5

Article No.: 63104180

Cable lug; Suitable crimping insert: PEW 12.060; For cross-section (min./max.): 1.50mm² - 2.50mm²; blue; Electrolytic copper Tin-plated



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data
General information

Product type	Cable lug
Type of packaging	Bag
Delivery Unit	100
Suitable crimping insert	PEW 12.060
Industry segment	Agricultural & Farm Machinery

Electrical parameters

applicable up to voltage	400 V
--------------------------	-------

Product design

Total length	0.906 in
Screw hole size	M5
For cross-section (min.)	1.5 mm ²
For cross-section (max.)	2.5 mm ²
Connector material	Electrolytic copper
Insulation material	Polyamide
Surface protection	Tin-plated
Colour description	blue
cable lug design	Ring cable lug

Product features

Flame-retardant	Yes
Flame retardance according to	UL 94 V-0
UV-resistant	No
Chemical resistant	Yes
corrosion resistant	Yes

Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	No
EAC certified	Not required
EAC certification number	Отказное письмо № 39
UL recognized	No
UL listed	Yes
UL certification	according to UL 486A/486B (e-file number: E334109) according to UL 486C (e-file number: E334109)
UL category control number	ZMVV7
cUR recognized	No
cUL listed	Yes
cUL certification	according to CSA-C22.2 No. 188 (e-file number: E334109) according to CSA C22.2 No. 65 (e-file number: E334109)
CSA certified	No
VDE certified	No

Ring cable lugs

Article No.	Name	Suitable crimping insert	For cross-section (min.)	For cross-section (max.)	Colour description	Delivery Unit
63104010	RING CABLE LUGS L-RZ 3	PEW 12.064	0.25 mm ²	0.75 mm ²	green	100
63104020	RING CABLE LUGS L-RZ 4	PEW 12.064	0.25 mm ²	0.75 mm ²	green	100
63104030	RING CABLE LUGS L-RZ 5	PEW 12.064	0.25 mm ²	0.75 mm ²	green	100
63104040	RING CABLE LUGS L-RA 3	PEW 12.060	0.5 mm ²	1.5 mm ²	red	100
63104050	RING CABLE LUGS L-RA 35	PEW 12.060	0.5 mm ²	1.5 mm ²	red	100
63104060	RING CABLE LUGS L-RA 4	PEW 12.060	0.5 mm ²	1.5 mm ²	red	100
63104070	RING CABLE LUGS L-RA 5	PEW 12.060	0.5 mm ²	1.5 mm ²	red	100
63104080	RING CABLE LUGS L-RA 6	PEW 12.060	0.5 mm ²	1.5 mm ²	red	100
63104160	RING CABLE LUGS L-RB 3	PEW 12.060	1.5 mm ²	2.5 mm ²	blue	100
63104170	RING CABLE LUGS L-RB 4	PEW 12.060	1.5 mm ²	2.5 mm ²	blue	100
63104180	RING CABLE LUGS L-RB 5	PEW 12.060	1.5 mm ²	2.5 mm ²	blue	100
63104190	RING CABLE LUGS L-RB 6	PEW 12.060	1.5 mm ²	2.5 mm ²	blue	100
63104200	RING CABLE LUGS L-RB 8	PEW 12.060	1.5 mm ²	2.5 mm ²	blue	100
63104340	RING CABLE LUGS L-RC 4	PEW 12.060	4 mm ²	6 mm ²	yellow	50
63104350	RING CABLE LUGS L-RC 5	PEW 12.060	4 mm ²	6 mm ²	yellow	50
63104360	RING CABLE LUGS L-RC 6	PEW 12.060	4 mm ²	6 mm ²	yellow	50
63104370	RING CABLE LUGS L-RC 8	PEW 12.060	4 mm ²	6 mm ²	yellow	50
63104380	RING CABLE LUGS L-RC 10	PEW 12.060	4 mm ²	6 mm ²	yellow	50

V1.1