

FORK CABLE LUGS L-RC 5F
Article No.: 63105220

Cable lug; Suitable crimping insert: PEW 12.060; For cross-section (min./max.): 4mm² - 6mm²; yellow; Electrolytic copper Tin-plated


Details
Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data

General information

Product type	Cable lug
Type of packaging	Cardboard packaging
Delivery Unit	50
Suitable crimping insert	PEW 12.060

Electrical parameters**Product design**

Total length	1.051 in
Screw hole size	M5
For cross-section (min.)	4 mm ²
For cross-section (max.)	6 mm ²
Connector material	Electrolytic copper
Insulation material	Polyamide
Surface protection	Tin-plated
Colour description	yellow
cable lug design	Fork cable lug

Product features

Flame-retardant	Yes
Flame retardance according to	UL 94 V-0
UV-resistant	No
Chemical resistant	Yes
corrosion resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	No
EAC certified	Not required

EAC certification number	Отказное письмо № 39
UL recognized	No
UL listed	Yes
UL certification	according to UL 486A/486B (e-file number: E334109) according to UL 486C (e-file number: E334109)
UL category control number	ZMVV7
cUR recognized	No
cUL listed	Yes
cUL certification	according to CSA-C22.2 No. 188 (e-file number: E334109) according to CSA C22.2 No. 65 (e-file number: E334109)
CSA certified	No
VDE certified	No

Fork cable lugs

Article No.	Name	Suitable crimping insert	For cross-section (min.)	For cross-section (max.)	Colour description	Delivery Unit
63105010	FORK CABLE LUGS L-RZ 3F	PEW 12.064	0.25 mm ²	0.75 mm ²	green	100
63105020	FORK CABLE LUGS L-RZ 4F	PEW 12.064	0.25 mm ²	0.75 mm ²	green	100
63105040	FORK CABLE LUGS L-RA 35F	PEW 12.060	0.5 mm ²	1.5 mm ²	red	100
63105050	FORK CABLE LUGS L-RA 4F	PEW 12.060	0.5 mm ²	1.5 mm ²	red	100
63105060	FORK CABLE LUGS L-RA 5F	PEW 12.060	0.5 mm ²	1.5 mm ²	red	100
63105070	FORK CABLE LUGS L-RA 6F	PEW 12.060	0.5 mm ²	1.5 mm ²	red	100
63105110	FORK CABLE LUGS L-RB 3F	PEW 12.060	1.5 mm ²	2.5 mm ²	blue	100
63105120	FORK CABLE LUGS L-RB 35F	PEW 12.060	1.5 mm ²	2.5 mm ²	blue	100
63105130	FORK CABLE LUGS L-RB 4F	PEW 12.060	1.5 mm ²	2.5 mm ²	blue	100
63105140	FORK CABLE LUGS L-RB 5F	PEW 12.060	1.5 mm ²	2.5 mm ²	blue	100
63105150	FORK CABLE LUGS L-RB 6F	PEW 12.060	1.5 mm ²	2.5 mm ²	blue	100
63105210	FORK CABLE LUGS L-RC 4F	PEW 12.060	4 mm ²	6 mm ²	yellow	50
63105220	FORK CABLE LUGS L-RC 5F	PEW 12.060	4 mm ²	6 mm ²	yellow	50
63105230	FORK CABLE LUGS L-RC 6F	PEW 12.060	4 mm ²	6 mm ²	yellow	50

V1.1