

CABLE LUGS KB35-10R DIN 46234**Article No.:** 63204415

Cable lug; Suitable crimping insert: ; For cross-section (min./max.): 35mm² - 35mm²;
Electrolytic copper Tin-plated

**CE****Details****Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data**General information**

Product type	Cable lug
Type of packaging	Cardboard packaging
Delivery Unit	100

Electrical parameters**Product design**

Marking	10-35
Screw hole size	M10
For cross-section (min.)	35 mm ²
For cross-section (max.)	35 mm ²
Connector material	Electrolytic copper
Surface protection	Tin-plated
cable lug design	Crimp cable lug

Product features

Flame-retardant	Yes
UV-resistant	Yes
Chemical resistant	Yes
corrosion resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	Yes
EAC certified	Not required

EAC certification number	Отказное письмо № 39
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No

Solderless cable lugs KB

Article No.	Name	Suitable crimping insert	For cross-section (min.)	For cross-section (max.)	Screw hole size	Delivery Unit
63204015	CABLE LUGS KB 1-2.5R DIN 46234	PEW 12.1071	0.5 mm ²	1.5 mm ²	M2,5	100
63204025	CABLE LUGS KB 1-3R DIN 46234	PEW 12.1071	0.5 mm ²	1.5 mm ²	M3	100
63204035	CABLE LUGS KB 1-3.5R DIN 46234	PEW 12.1071	0.5 mm ²	1.5 mm ²	M3,5	100
63204045	CABLE LUGS KB 1-4R DIN 46234	PEW 12.1071	0.5 mm ²	1.5 mm ²	M4	100
63204055	CABLE LUGS KB 1-5R DIN 46234	PEW 12.1071	0.5 mm ²	1.5 mm ²	M5	100
63204065	CABLE LUGS KB 1-6R	PEW 12.1071	0.5 mm ²	1.5 mm ²	M6	100
63204075	CABLE LUGS KB 1-8R	PEW 12.1071	0.5 mm ²	1.5 mm ²	M8	100
63204085	CABLE LUGS KB 1-10R	PEW 12.1071	0.5 mm ²	1.5 mm ²	M10	100
63204095	CABLE LUGS KB2.5-3R DIN 46234	PEW 12.1071	1.5 mm ²	2.5 mm ²	M3	100
63204105	CABLE LUGS KB2.5-3.5R DIN46234	PEW 12.1071	1.5 mm ²	2.5 mm ²	M3,5	100
63204115	CABLE LUGS KB2.5-4R DIN 46234	PEW 12.1071	1.5 mm ²	2.5 mm ²	M4	100
63204125	CABLE LUGS KB 2.5-5R	PEW 12.1071	1.5 mm ²	2.5 mm ²	M5	100
63204135	CABLE LUGS KB2.5-6R DIN 46234	PEW 12.1071	1.5 mm ²	2.5 mm ²	M6	100
63204145	CABLE LUGS KB2.5-8R DIN 46234	PEW 12.1071	1.5 mm ²	2.5 mm ²	M8	100
63204155	CABLE LUGS KB2.5-10R	PEW 12.1071	1.5 mm ²	2.5 mm ²	M10	100
63204165	CABLE LUGS KB2.5-12R	PEW 12.1071	1.5 mm ²	2.5 mm ²	M12	100
63204175	CABLE LUGS KB6-4R	PEW 12.1071	4 mm ²	6 mm ²	M4	100
63204185	CABLE LUGS KB6-5R	PEW 12.1071	4 mm ²	6 mm ²	M5	100
63204195	CABLE LUGS KB6-6R	PEW 12.1071	4 mm ²	6 mm ²	M6	100
63204205	CABLE LUGS KB6-8R	PEW 12.1071	4 mm ²	6 mm ²	M8	100
63204215	CABLE LUGS KB6-10R DIN 46234	PEW 12.1071	4 mm ²	6 mm ²	M10	100
63204225	CABLE LUGS KB6-12R	PEW 12.1071	4 mm ²	6 mm ²	M12	100
63204235	CABLE LUGS KB10-5R DIN 46234	PEW 12.1071	10 mm ²	10 mm ²	M5	100
63204245	CABLE LUGS KB10-6R DIN 46234	PEW 12.1071	10 mm ²	10 mm ²	M6	100
63204255	CABLE LUGS KB10-8R DIN 46234	PEW 12.1071	10 mm ²	10 mm ²	M8	100
63204265	CABLE LUGS KB10-10R DIN 46234	PEW 12.1071	10 mm ²	10 mm ²	M10	100
63204275	CABLE LUGS KB10-12R DIN 46234	PEW 12.1071	10 mm ²	10 mm ²	M12	100
63204285	CABLE LUGS KB16-5R DIN 46234	PEW 12.033	16 mm ²	16 mm ²	M5	100
63204295	CABLE LUGS KB16-6R DIN 46234	PEW 12.033	16 mm ²	16 mm ²	M6	100
63204305	CABLE LUGS KB16-8R DIN 46234	PEW 12.033	16 mm ²	16 mm ²	M8	100

Article No.	Name	Suitable crimping insert	For cross-section (min.)	For cross-section (max.)	Screw hole size	Delivery Unit
63204315	CABLE LUGS KB16-10R DIN 46234	PEW 12.033	16 mm ²	16 mm ²	M10	100
63204325	CABLE LUGS KB16-12R DIN 46234	PEW 12.033	16 mm ²	16 mm ²	M12	100
63204335	CABLE LUGS KB25-5R DIN 46234	PEW 12.033	25 mm ²	25 mm ²	M5	100
63204345	CABLE LUGS KB25-6R DIN 46234	PEW 12.033	25 mm ²	25 mm ²	M6	100
63204355	CABLE LUGS KB 25-8R DIN 46234	PEW 12.033	25 mm ²	25 mm ²	M8	100
63204365	CABLE LUGS KB25-10R DIN 46234	PEW 12.033	25 mm ²	25 mm ²	M10	100
63204375	CABLE LUGS KB25-12R DIN 46234	PEW 12.033	25 mm ²	25 mm ²	M12	100
63204395	CABLE LUGS KB35-6R DIN 46234		35 mm ²	35 mm ²	M6	100
63204405	CABLE LUGS KB35-8R DIN 46234		35 mm ²	35 mm ²	M8	100
63204415	CABLE LUGS KB35-10R DIN 46234		35 mm ²	35 mm ²	M10	100
63204425	CABLE LUGS KB35-12R DIN 46234		35 mm ²	35 mm ²	M12	100
63204445	CABLE LUGS KB50-6R DIN 46234		50 mm ²	50 mm ²	M6	100
63204455	CABLE LUGS KB50-8R DIN 46234		50 mm ²	50 mm ²	M8	100
63204465	CABLE LUGS KB50-10R DIN 46234		50 mm ²	50 mm ²	M10	100
63204475	CABLE LUGS KB50-12R DIN 46234		50 mm ²	50 mm ²	M12	100
63204505	CABLE LUGS KB70-8R DIN 46234		70 mm ²	70 mm ²	M8	100
63204515	CABLE LUGS KB70-10R DIN 46234		70 mm ²	70 mm ²	M10	100
63204545	CABLE LUGS KB95-8R DIN 46234		95 mm ²	95 mm ²	M8	50
63204555	CABLE LUGS KB95-10R DIN 46234		95 mm ²	95 mm ²	M10	50
63204565	CABLE LUGS KB95-12R DIN 46234		95 mm ²	95 mm ²	M12	50
63204595	CABLE LUGS KB120-10R DIN 46234		120 mm ²	120 mm ²	M10	25
63204605	CABLE LUGS KB120-12R DIN 46234		120 mm ²	120 mm ²	M12	25
63204625	CABLE LUGS KB150-10R DIN 46234		150 mm ²	150 mm ²	M10	25
63204655	CABLE LUGS KB185-10R DIN 46234		185 mm ²	185 mm ²	M10	20

V1.1