

**SILVYN® K-EM 42 BK**

**Article No.:** 65500265

End sleeve; Nominal size: 42.5; Thermoplastic elastomers;



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

**Technical Data**

**General information**

Brand	SILVYN®
Product type	End sleeve
Delivery with lock nut	No
Including o-ring	No
Type of packaging	Bag

---

Delivery Unit	25
Mounting method	push on

---

**Electrical parameters****Product design**

---

With bending protection	No
Total length	1.811 in
Nominal size	42.5 "
Clamping range min.	0.394 in
Clamping range max.	1.457 in
EMC shielding	No
Body material	Thermoplastic elastomers
Body material, short form	TPE

---

**Product features**

---

Suitable for EX-applications	No
Short term temperature max.	150 °C
Flame-retardant	Yes
Flame retardance according to	UL 94 HB
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

---

**Certifications and standards**

---

CE marking	No
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No

---

---

VDE certified	No
GGVS certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

---

**SILVYN® K-EM**

Article No.	Name	Nominal size	Clamping range min.	Delivery Unit	Clamping range max.
65500205	SILVYN® K-EM 10 BK	10 "	0.039 in	50	0.315 in
65500215	SILVYN® K-EM 13 BK	13 "	0.039 in	50	0.394 in
65500220	SILVYN® K-EM 16 GY	15.8 "	0.157 in	50	0.472 in
65500225	SILVYN® K-EM 16 BK	15.8 "	0.157 in	50	0.472 in
65500230	SILVYN® K-EM 21 GY	21.2 "	0.236 in	50	0.65 in
65500235	SILVYN® K-EM 21 BK	21.2 "	0.236 in	50	0.65 in
65500240	SILVYN® K-EM 28 GY	28.5 "	0.236 in	25	0.906 in
65500245	SILVYN® K-EM 28 BK	28.5 "	0.236 in	25	0.906 in
65500250	SILVYN® K-EM 34 GY	34.5 "	0.236 in	25	1.142 in
65500255	SILVYN® K-EM 34 BK	34.5 "	0.236 in	25	1.142 in
65500265	SILVYN® K-EM 42 BK	42.5 "	0.394 in	25	1.457 in

V1.1