

**SILVYN® FLEXILOK M 16X1.5 /16 BK**

**Article No.:** 65500425

Conduit connector; M 16; Nominal size: 16; Suitable for protective cable conduit size: 16; Polyamide; Halogen-free; UV-resistant; IP 66;



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

**Technical Data**

**General information**

Brand	SILVYN®
Product type	Conduit connector
Delivery with lock nut	No
Including o-ring	No

Delivery Unit	10
Mounting method	in threaded borehole

### Electrical parameters

#### Product design

suitable for protective conduit size	16
With bending protection	No
Bending protection fixed installation	No
Flexibly installed bending protection	No
Slotted	No
Resistance against hot swarf	No
Divisible conduit gland	No
Rotatable thread	No
Total length	1.772 in
Overall width	0.906 in
Clear width	0.433 in
Nominal size	16 "
Thread type	Metric
Thread size	M 16
Pitch of thread	1,5
Thread length	0.472 in
Thread standard	DIN EN 60423
Lockable (two-part)	No
EMC shielding	No
For conduit outer diameter	0.63 in
Body material	Polyamide
Body material, short form	PA
Colour description	black

#### Product features

IP protection rating	IP 66
----------------------	-------

---

Suitable for EX-applications	No
Flame-retardant	Yes
Flame retardance according to	UL 94 V-2
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
Strain relief	No

---

**Certifications and standards**

CE marking	Yes
UL recognized	Yes
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
DNV-certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

---

**SILVYN® FLEXILOK M**

Article No.	Name	Thread size	Colour description	suitable for protective conduit size	Delivery Unit
65500405	SILVYN® FLEXILOK M 16X1.5 /13 BK	M 16	black	13	10
65500410	SILVYN® FLEXILOK M 20X1.5 /13 GY	M 20	gray	13	10
65500425	SILVYN® FLEXILOK M 16X1.5 /16 BK	M 16	black	16	10
65500435	SILVYN® FLEXILOK M 20X1.5 /16 BK	M 20	black	16	10
65500436	SILVYN® FLEXILOK M 20X1.5 /20 BK	M 20	black	20	10
65500445	SILVYN® FLEXILOK M 20X1.5 /21 BK	M 20	black	21	10
65500455	SILVYN® FLEXILOK M 25X1.5 /28 BK	M 25	black	28	10
65500456	SILVYN® FLEXILOK M 25X1.5 /25 BK	M 25	black	25	10
65500458	SILVYN® FLEXILOK M 40X1.5 /42 BK	M 40	black	42	2
65500459	SILVYN® FLEXILOK M 50X1.5 /54 BK	M 50	black	54	1
65500460	SILVYN® FLEXILOK M 32X1.5 /34 GY	M 32	gray	34	10
65500464	SILVYN® FLEXILOK M 32X1.5 /32 BK	M 32	black	32	10
65500465	SILVYN® FLEXILOK M 32X1.5 /34 BK	M 32	black	34	10
65500610	SILVYN® FLEXILOK M 25X1.5 /28 GY	M 25	gray	28	10

V1.1