

SILVYN® KLICK-RH 28 GY
Article No.: 65500635

Mounting bracket; Nominal size: 28; Polyamide


Details
Benefits

- One-piece and therefore without losable small parts.
- Easy closing with a click mechanism.
- Tear-resistant fastening of parallel corrugated protective cable conduits by means of the positioning rib in the mounting bracket.
- Easy assembly using M5/M6 screws on the housing or by inserting into C-profile rails.
- Groove system enables installation directly next to each other.

Application

- Suitable for fastening and/or guiding a parallel corrugated protective cable conduit.
- For use with SILVYN® RILL PA 6 and SILVYN® RILL PA 12 protective cable conduits.
- Suitable for medium mechanical stress.
- Black variants are suitable for outdoor use.

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SILVYN®
Product type	Mounting bracket
Delivery with lock nut	No
Including o-ring	No
Type of packaging	Bag
Delivery Unit	25
Mounting method	screw

Electrical parameters

Product design

Total length	1.654 in
Overall width	0.63 in
Overall height	1.594 in
Nominal size	28 "
Body material	Polyamide
Body material, short form	PA
Colour description	gray

Product features

Suitable for EX-applications	No
Flame-retardant	Yes
Flame retardance according to	UL 94 HB
UV-resistant	No
Chemical resistant	Yes

Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	No
EHEDG certified	No

SILVYN® KLICK-RH

Article No.	Name	Nominal size	Colour description	Delivery Unit
65500630	SILVYN® KLICK-RH 10 GY	10 "	gray	50
65500631	SILVYN® KLICK-RH 13 GY	13 "	gray	50
65500632	SILVYN® KLICK-RH 16 GY	16 "	gray	50
65500633	SILVYN® KLICK-RH 18 GY	18 "	gray	50
65500634	SILVYN® KLICK-RH 21 GY	21 "	gray	50
65500635	SILVYN® KLICK-RH 28 GY	28 "	gray	25
65500636	SILVYN® KLICK-RH 34 GY	34 "	gray	25
65500637	SILVYN® KLICK-RH 42 GY	42 "	gray	25
65500638	SILVYN® KLICK-RH 54 GY	54 "	gray	10
65500639	SILVYN® KLICK-RH 10 BK	10 "	black	50
65500640	SILVYN® KLICK-RH 13 BK	13 "	black	50
65500641	SILVYN® KLICK-RH 16 BK	16 "	black	50
65500642	SILVYN® KLICK-RH 18 BK	18 "	black	50
65500643	SILVYN® KLICK-RH 21 BK	21 "	black	50
65500644	SILVYN® KLICK-RH 28 BK	28 "	black	25
65500645	SILVYN® KLICK-RH 34 BK	34 "	black	25
65500646	SILVYN® KLICK-RH 42 BK	42 "	black	25
65500647	SILVYN® KLICK-RH 54 BK	54 "	black	10

V1.1