

SILVYN® FLEXILOK PG 21 /28 BK

Article No.: 68100095

Conduit connector; PG 21; Nominal size: 28; Suitable for protective cable conduit size: 28; Polyamide; Halogen-free; UV-resistant; IP 66;



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SILVYN®
Product type	Conduit connector
Delivery with lock nut	No
Including o-ring	No

Type of packaging	Bag
Delivery Unit	10
Mounting method	in threaded borehole

Electrical parameters**Product design**

suitable for protective conduit size	28
With bending protection	No
Bending protection fixed installation	No
Flexibly installed bending protection	No
Slotted	No
Resistance against hot swarf	No
Divisible conduit gland	No
Rotatable thread	No
Total length	2.008 in
Overall width	1.417 in
Clear width	0.886 in
Nominal size	28 "
Thread type	PG
Thread size	PG 21
Pitch of thread	1,588
Thread length	0.472 in
Lockable (two-part)	No
EMC shielding	No
For conduit outer diameter	1.102 in
Body material	Polyamide
Body material, short form	PA
Colour description	black

Product features

IP protection rating	IP 66
----------------------	-------

Suitable for EX-applications	No
Flame-retardant	Yes
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
Strain relief	No

Certifications and standards

CE marking	Yes
UL recognized	Yes
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
DNV-certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

SILVYN® FLEXILOK PG

Article No.	Name	Thread size	Colour description	suitable for protective conduit size	Delivery Unit
65500390	SILVYN® FLEXILOK PG 11 /16 GY	PG 11	gray	16	10
65500395	SILVYN® FLEXILOK PG 11 /16 BK	PG 11	black	16	10
65500475	SILVYN® FLEXILOK PG 9 /13 BK	PG 9	black	13	10
65500485	SILVYN® FLEXILOK PG 11 /13 BK	PG 11	black	13	10
68100085	SILVYN® FLEXILOK PG 16 /21 BK	PG 16	black	21	10
68100095	SILVYN® FLEXILOK PG 21 /28 BK	PG 21	black	28	10
68880005	SILVYN® FLEXILOK PG 29 /34 BK	PG 29	black	34	10

V1.1