

**HA 16 HP TE HOOD W/SNG LVR, 3/4in**

**Article No.:** 704804NP

`\${ctx.productData.top5String}`



**Details**

**Benefits**

- The EPIC® H-A series of rectangular connectors includes slim and space-saving housings that are suitable for confined spaces.
- The cable coupler hood can be connected to many of the most popular hoods on the market.
- With threaded borehole for use with a corresponding cable gland.
- It is locked by means of a single lever made of steel.
- Meets protection class IP 65 when locked.
- The user-friendly design with a good grip makes the plug connection easy to connect and release.
- UL certification according to technical data enables the product to be used on the North American market.

**Application**

- For protecting the connector insert against environmental influences.
- For use with many EPIC® rectangular connector inserts.
- For connecting devices and machines to a power supply in various applications
- Suitable for outdoor use.

**Notes**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

### Remarks

### Technical Data

#### General information

|              |                    |
|--------------|--------------------|
| Brand        | EPIC®              |
| Product type | Cable coupler hood |
| Design size  | 16A                |

#### Electrical parameters

#### Product design

|                                    |                    |
|------------------------------------|--------------------|
| With cable gland                   | No                 |
| Number of cable entries            | 1 pc.              |
| Number of cable entries at the top | 1                  |
| Number of cable entries sideways   | 0                  |
| With levers                        | Yes                |
| Locking mechanism                  | Single lever       |
| Number of locking bolts            | 0                  |
| Total length                       | 3.11 in            |
| Overall width                      | 1.161 in           |
| Overall height                     | 2.087 in           |
| Thread type                        | NPT                |
| Thread size                        | NPT 3/4"           |
| Type of housing                    | Cable coupler hood |
| Connector housing design           | Straight           |
| With thread                        | Yes                |

|                                     |                                |
|-------------------------------------|--------------------------------|
| With hinged lid                     | No                             |
| Connection design                   | High                           |
| With neck                           | Yes                            |
| Screen contact                      | No                             |
| EMC shielding                       | No                             |
| Material connecting piece           | Brass                          |
| Material connecting piece shortname | CuZn                           |
| Housing main material               | Aluminum                       |
| Housing base material, short form   | Al                             |
| Housing coating                     | Powder-coated                  |
| Lever material                      | Steel                          |
| Material sealing                    | Acrylonitrile butadiene rubber |
| Colour housing                      | gray                           |
| Housing RAL color                   | RAL 9006                       |

#### Product features

|                                   |             |
|-----------------------------------|-------------|
| Protection rating (IP), unmounted | IP 65       |
| IP protection rating mounted      | IP 65       |
| Short term temperature peak       | 125 °C      |
| Operating temperature max.        | -40 °C      |
| Operation temperature max.        | 100 °C      |
| UV-resistant                      | Yes         |
| Chemical resistant                | No          |
| Acid-resistant                    | No          |
| Corrosion-resistant according to  | DIN EN 6988 |
| corrosion resistant               | Yes         |
| Halogenfree                       | Yes         |
| Impact proof                      | Yes         |
| Vibration protection              | Yes         |

#### Certifications and standards

|               |     |
|---------------|-----|
| CE marking    | Yes |
| UR recognized | Yes |

---

|                                   |   |
|-----------------------------------|---|
| UR certification                  | according to UL 1977 (e-file number: E75770)<br>according to UL 50E (e-file number: E75770) |
| UL category control number        | ECBT2   |
| cUR recognized                    | Yes   |
| cUR certification                 | according to CSA C22.2 No. 182.3 (e-file number: E75770)                                    |
| cUR category control number       | ECBT8   |
| CSA certified                     | No  |
| VDE certified                     | Yes   |
| VDE registration number           | B437  |
| Product standard according to IEC | IEC 61984   |
| TÜV certified                     | No  |

---

---

**EPIC® H-A 16 TBF (NPT)**

| Article No. | Name                              |
|-------------|-----------------------------------|
| 105630NP    | HA 16 CC HOOD W/SNG LVR, 1/2in    |
| 704802NP    | HA 16 HIGH PROF CABLE COUPLE      |
| 704804NP    | HA 16 HP TE HOOD W/SNG LVR, 3/4in |

V1.1