

FCC SMC LS 200mm 16-25 sign

Article No.: 83251456

Embossing label; Number of characters: 25; Overall height: 9.9mm;



Details

Notes

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Remarks

Included in FLEXIMARK® sample bag (article no. M3251010).

Labeling service is already included in the price.

The length of the markers depends on the number of characters.

All characters are printed in upper case.

1 PU contains 1 marker, there is no minimum quantity.

Markers are sorted and delivered.

Cable ties included: steel cable ties LS 4.6-200 (article no. 61812950).

Blank variant article no. 83251575 and 83251576.

Available characters: A-Ü 0-9 + - / . : , = grounding character.

Order process: Customer-specific data is emailed as an Excel file to the responsible LAPP employee at the same time as the order

The order template for print orders can be found in the "Customer-specific labeling" section under the "Guide" tab. Please use the following link: <https://www.lapp.com/de/de/produkte/kennzeichnungssysteme/kabel-und-einzeladerekennzeichnung/kundenspezifische-kennzeichnungen/c/124766>

Technical Data

General information

Brand	FLEXIMARK®
Product type	Embossing label
Scope of delivery	including cable ties
Delivery Unit	1
pieces per PU	1 pc.
Mounting method	with cable ties
Printing procedure	Embossing
Marking for	Conductors Cables

Electrical parameters

Product design

Number of text lines	1
Number of characters	25
Labeling	Customized
Label type	Cable Label
Label design	Rectangular
Character height	0.165 in
Spacing between characters	0.039 in
Overall height	0.39 in
Material label	Stainless steel
Cable tie width	0.311 in

Product features

Flame-retardant	Yes
UV-resistant	Yes
Chemical resistant	Yes
Acid-resistant	Yes
Alkali resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
salt water resistant	Yes
Waterproof	Yes
Self-adhesive	No

Certifications and standards

CE marking	No
UL recognized	No
UL listed	No
Ecolab certified	No

FLEXIMARK® stainless steel FCC - with cable ties

Article No.	Name	Number of characters	Overall height	Overall width	pieces per PU
83251456	FCC SMC LS 200mm 16-25 sign	25	0.39 in		1 pc.

V1.1