

**Characterholder PTE 9.5-285 TR**

**Article No.:** 83252081

Sign/label holder; Overall height: 9.5mm; Polyethylene



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

Suitable for FLEXIMARK® Flexilabels LFL and DYMO® industrial tapes.

**Technical Data**

**General information**

Brand	FLEXIMARK®
Product type	Sign/label holder
Type of packaging	Bag
Delivery Unit	1

pieces per PU	10 pc.
Mounting method	with cable ties
Marking for	Conductors Cables Conduits

### Electrical parameters

#### Product design

Transparent	Yes
Total length	11.22 in
Overall height	0.374 in
Material	Polyethylene
Material label	Polyethylene
Colour description	transparent
for cable tie width	0.102 in

#### Product features

Flame-retardant	No
UV-resistant	Yes
UV-resistant according to	EN ISO 4892-2, method A (color change permitted)
Chemical resistant	Yes
Acid-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
Waterproof	No

#### Certifications and standards

CE marking	No
Ecolab certified	No

**FLEXIMARK® Character holders PTE**

Article No.	Name	Number of characters	Overall width	Overall height	pieces per PU
83252027	CharacterHolder PTE 12-1000 TR			0.472 in	10 pc.
83252028	Character Holder PTE 12-285 TR			0.472 in	10 pc.
83252081	Characterholder PTE 9.5-285 TR			0.374 in	10 pc.
83252084	Characterholder PTE 9.5-1000TR			0.374 in	10 pc.
83259952	CharacterHolder PTE 12-10000 T			0.472 in	
83259953	CharacterHolder PTE 19-5000 TR			0.748 in	
83259960	CharacterHolder PTE 6-15000 TR				
83259961	CharacterHolder PTE 9.5-15000				

V1.1