

Character holder PTEF 9.5x38mm
Article No.: 83254962

Sign/label holder; Overall width: 50mm; Overall height: 12.2mm; Polyethylene


Details
Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

PTEF 9.5-35 contained in the FLEXIMARK® sample bag (article no. M3251010).

Fastening with screws and rivets when using end plugs.

Technical Data

General information

Brand	FLEXIMARK®
Product type	Sign/label holder
Scope of delivery	without cable tie
Type of packaging	Cardboard packaging
Delivery Unit	1
pieces per PU	50 pc.
Mounting method	with cable ties
Marking for	Conductors Cables Conduits
Industry segment	Assembly Machines

Electrical parameters

Product design

Transparent	Yes
Overall width	1.969 in
Overall height	0.48 in
Max. label height	0.374 in
Material	Polyethylene
Colour description	transparent
for cable tie width	0.102 in

Product features

Flame-retardant	No
UV-resistant	Yes
UV-resistant according to	EN ISO 4892-2, method A (color change permitted)
Chemical resistant	Yes

Acid-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
salt water resistant	Yes
Waterproof	Yes

Certifications and standards

CE marking	No
Ecolab certified	No

FLEXIMARK® Character holders PTEF

Article No.	Name	Number of characters	Overall width	Max. label height	Overall height	pieces per PU
83254960	Character holder PTEF 9.5x18mm		1.181 in	0.374 in	0.48 in	50 pc.
83254961	Character holder PTEF 9.5x28mm		1.575 in	0.374 in	0.48 in	50 pc.
83254962	Character holder PTEF 9.5x38mm		1.969 in	0.374 in	0.48 in	50 pc.
83254963	Character holder PTEF 9.5x35mm		1.85 in	0.374 in	0.48 in	50 pc.
83254964	Character holder PTEF 9.5x58mm		2.756 in	0.374 in	0.48 in	50 pc.
83254965	Character holder PTEF 9.5x70mm		3.228 in	0.374 in	0.48 in	50 pc.
83254976	Character holder PTEF 12x28mm		1.575 in	0.472 in	0.583 in	50 pc.
83254977	Character holder PTEF 12x38mm		1.969 in	0.472 in	0.583 in	50 pc.
83254978	Character holder PTEF 12x58mm		2.756 in	0.472 in	0.583 in	50 pc.
83254982	Character holder PTEF 19x50mm		2.441 in	0.748 in	0.854 in	50 pc.

V1.1