

TCK 32 25x33,5mm YE**Article No.:** 83259882

Label for thermal transfer marking; Cable diameter: 0.157in - 0.276in; yellow; Polyester

**Details****Notes**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Remarks

Recommended colored ribbon: R71 110-360 resin BK (article no. 83259609)

More about the thermal transfer printing process / download: www.lappkabel.com/fleximark/fleximark-thermoprint

You can download the free full version of our FLEXIMARK® software in the "Printers and software" section under the "Guide" tab. Please use the following link: <https://www.lapp.com/de/de/produkte/kennzeichnungssysteme/drucker-und-software/c/114041>

Technical Data

General information

Brand	FLEXIMARK®
Product type	Label for thermal transfer marking
Type of packaging	Pulley
Delivery Unit	1
Number of labels per roll	1,200
Mounting method	wind
Printable with	Thermal transfer printer EOS 5 SQUIX
Printing procedure	Thermal Transfer Marking
Marking for	Conductors Cables

Electrical parameters

Product design

Label type	Wrapping Label
Label design	Rectangular
width printable area	0.984 in
labeling area height	0.5 in
Glue	Acrylic-based
Overall width	0.984 in
Overall height	1.319 in
Thickness	0.001 in
For min. cable outer diameter	0.157 in
For max. cable outer diameter	0.276 in

Material label	Polyester
Colour description	yellow

Product features

Installation temperature min.	10 °C
Flame-retardant	No
UV-resistant	Yes
UV-resistant according to	EN ISO 4892-2, method A (color change permitted)
Chemical resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
Waterproof	Yes
Self-adhesive	Yes

Certifications and standards

CE marking	No
UL recognized	No
UL listed	No
cUR recognized	No
Ecolab certified	No

FLEXIMARK® Wrapping labels TCK

Article No.	Name	For min. cable outer diameter	For max. cable outer diameter	Colour description	width printable area	labeling area height	pieces per PU	Number of pages per PU
83259874	TCK 32 25x33,5mm WH	0.157 in	0.276 in	white	0.984 in	0.5 in		
83259875	TCK 35 25x55mm WH	0.236 in	0.472 in	white	0.984 in	0.748 in		
83259876	TCK 40 25x94mm WH	0.315 in	0.827 in	white	0.984 in	0.984 in		
83259877	TCK 45 25x142,5mm WH	0.315 in	1.417 in	white	0.984 in	0.984 in		
83259882	TCK 32 25x33,5mm YE	0.157 in	0.276 in	yellow	0.984 in	0.5 in		
83259883	TCK 35 25x55mm YE	0.236 in	0.472 in	yellow	0.984 in	0.748 in		
83259890	TCK 48 34x93mm WH	0.315 in	0.827 in	white	1.339 in	1 in		

V1.1