

**UNIVERSAL STRIP BLADE SOLAR 1.5-6****Article No.:** 21920122Knife; Conductor cross-section 1.5mm<sup>2</sup> - 6mm<sup>2</sup>;**Details****Notes**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Trade product, not a LAPP product.

**Remarks**

Trade product, not a LAPP product.

---

## Technical Data

### General information

|               |              |
|---------------|--------------|
| Product type  | Knife        |
| Delivery Unit | 1            |
| suitable for  | Solar cables |

### Electrical parameters

#### Product design

|                          |                     |
|--------------------------|---------------------|
| For cross-section (min.) | 1.5 mm <sup>2</sup> |
| For cross-section (max.) | 6 mm <sup>2</sup>   |
| For insulation material  | Polyolefin          |

### Product features

#### Certifications and standards

|               |    |
|---------------|----|
| CE marking    | No |
| VDE certified | No |
| TÜV certified | No |

**UNIVERSAL STRIP stripping tool**

| Article No. | Name                                  | For cross-section (min.) | For cross-section (max.) | For insulation material                    | Product type   |
|-------------|---------------------------------------|--------------------------|--------------------------|--|----------------|
| 21920004    | UNIVERSAL STRIP BLADE PTFE 2.5-10     | 2.5 mm <sup>2</sup>      | 10 mm <sup>2</sup>       | Polytetrafluoroethylene                    | Knife          |
| 21920005    | UNIVERSAL STRIP W.OUT STRIPPING BLADE |                          |                          |  | Stripping tool |
| 21920006    | UNIVERSAL STRIP BLADE PTFE 0.03-2.08  | 0.03 mm <sup>2</sup>     | 2.08 mm <sup>2</sup>     | Polytetrafluoroethylene                    | Knife          |
| 21920009    | UNIVERSAL STRIP BLADE PVC 0.14-6      | 0.14 mm <sup>2</sup>     | 6 mm <sup>2</sup>        | Polyvinylchloride                          | Knife          |
| 21920120    | UNIVERSAL STRIP SOLAR                 | 1.5 mm <sup>2</sup>      | 6 mm <sup>2</sup>        | Polyolefin                                 | Stripping tool |
| 21920122    | UNIVERSAL STRIP BLADE SOLAR 1.5-6     | 1.5 mm <sup>2</sup>      | 6 mm <sup>2</sup>        | Polyolefin                                 | Knife          |
| 21920140    | UNIVERSAL STRIP ASI                   |                          |                          | Thermoplastic elastomers,Polyvinylchloride | Stripping tool |

V1.1