

**SKINDICHT® KUK PG 36/29 REDUCER**

**Article No.:** 51730110

Reducer; Inner thread: PG 29; Outer thread: PG 36; Polyamide; light gray



**CE**



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

**Technical Data**

**General information**

Brand	SKINDICHT®
Product type	Reducer
Delivery with lock nut	No
Including o-ring	No

Type of packaging	Bag
Delivery Unit	25
Mounting method	in threaded borehole

### Electrical parameters

#### Product design

Glass-fibre reinforced	Yes
Cable gland design	Straight
Inner thread	PG 29
Outer thread	PG 36
Total length	0.551 in
Overall width	2.224 in
Thread type	PG
Thread size	PG 36
Pitch of thread	1,588
Thread length	0.433 in
Body material	Polyamide
Body material, short form	PA
Surface protection	Uncoated
Colour description	light gray
RAL color	RAL 7035

#### Product features

Suitable for EX-applications	No
Temperature (min.)	-40 °C
Max. temperatur	100 °C
Flame-retardant	No
UV-resistant	No
Halogenfree	Yes
Oil resistant	Yes

---

**Certifications and standards**

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

**SKINDICHT® KUK**

Article No.	Name	Outer thread	Inner thread	Colour description	Delivery Unit
51730020	SKINDICHT® KUK PG 13.5/9 REDUCER	PG 13,5	PG 9	light gray	50
51730025	SKINDICHT® KUK PG 16/9 REDUCER	PG 16	PG 9	light gray	50
51730030	SKINDICHT® KUK PG 16/11 REDUCER	PG 16	PG 11	light gray	50
51730035	SKINDICHT® KUK PG 21/13.5 REDUCER	PG 21	PG 13,5	light gray	50
51730090	SKINDICHT® KUK PG 21/16 REDUCER	PG 21	PG 16	light gray	50
51730100	SKINDICHT® KUK PG 29/21 REDUCER	PG 29	PG 21	light gray	25
51730110	SKINDICHT® KUK PG 36/29 REDUCER	PG 36	PG 29	light gray	25

V1.1