

CABLE TIES TY-RAP® TYB 23 M 92X2.4 NA

Article No.: 61715000

Cable ties; Cable tie width: 0.094in; Total length: 92mm; natural; Polyamide; Halogen-free;



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data
General information

Product type	Cable ties
Delivery Unit	1,000
suitable tools	TY GUN ERG 50 cable tie pliers
Industry segment	Food & Beverage Healthcare & Pharma Robotics Solar

Electrical parameters
Product design

Total length	3.622 in
for bundling diameter (min.)	0.079 in
for bundling diameter (max.)	0.63 in
Material	Polyamide
with metal parts	Yes
Cable tie width	0.094 in
Colour description	natural

Product features

Flame-retardant	Yes
Flame retardance according to	UL 94 V-2
UV-resistant	No
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	No
UL recognized	Yes
UL AWM certification	according to UL 1565 (e-file number: E49405) according to UL 62275 (e-file number: E49405)
UL listed	No
cUR recognized	Yes
cUR certification	according to CSA C22.2 No. 62275 (e-file number: E49405) according to CSA C22.2 No. 18.5 (e-file number: E49405)
cUL listed	No
CSA certified	No
VDE certified	No
DNV-certified	No
Ecolab certified	No

TY-RAP® Cable ties with steel nose

Article No.	Name	for bundling diameter (min.)	for bundling diameter (max.)	Cable tie width	Total length	Colour description	Delivery Unit
61715000	CABLE TIES TY-RAP® TYB 23 M 92X2.4 NA	0.079 in	0.63 in	0.094 in	3.622 in	natural	1,000
61715060	CABLE TIES TY-RAP® TYB 24 M 140X3.6 NA	0.079 in	1.142 in	0.142 in	5.512 in	natural	1,000
61715120	CABLE TIES TY-RAP® TYB 25 M 186X4.8 NA	0.138 in	1.772 in	0.189 in	7.323 in	natural	1,000
61715180	CABLE TIES TY-RAP® TY 26 M 284X3.6 NA	0.079 in	2.992 in	0.142 in	11.181 in	natural	1,000
61715240	CABLE TIES TY-RAP® TY 27 M 340X7.0 NA	0.236 in	3.543 in	0.276 in	13.386 in	natural	500
61715300	CABLE TIES TY-RAP® TY 28 M 361X4.8 NA	0.138 in	4.016 in	0.189 in	14.213 in	natural	1,000
61715360	CABLE TIES TY-RAP® TY 29 M 771X6.9 NA	0.236 in	9.016 in	0.272 in	30.354 in	natural	500
61716250	CABLE TIES TY-RAP® TY 232 M 203X2.4 NA	0.079 in	1.969 in	0.094 in	7.992 in	natural	1,000
61716310	CABLE TIES TY-RAP® TY 234 M 356X2.4 NA	0.079 in	4.016 in	0.094 in	14.016 in	natural	1,000
61716370	CABLE TIES TY-RAP® TY 242 M 208X3.6 NA	0.079 in	1.969 in	0.142 in	8.189 in	natural	1,000
61716430	CABLE TIES TY-RAP® TY 244 M 366X3.6 NA	0.079 in	4.055 in	0.142 in	14.488 in	natural	1,000
61716490	CABLE TIES TY-RAP® TY 253 M 295X4.8 NA	0.138 in	3.071 in	0.189 in	11.417 in	natural	1,000
61716550	CABLE TIES TY-RAP® TY 272 M 223X7.6 NA	0.236 in	1.969 in	0.299 in	8.78 in	natural	500
61723010	CABLE TIES TY-RAP® TYB 23 MX 92X2.3 BK	0.079 in	0.63 in	0.091 in	3.622 in	black	1,000
61723020	CABLE TIES TY-RAP® TYB 24 MX 140X3.6 BK	0.079 in	1.142 in	0.142 in	5.512 in	black	1,000
61723030	CABLE TIES TY-RAP® TYB 25 MX 186X4.8 BK	0.138 in	1.772 in	0.189 in	7.323 in	black	1,000
61723040	CABLE TIES TY-RAP® TY 26 MX 284X3.6 BK	0.079 in	2.992 in	0.142 in	11.181 in	black	1,000
61723050	CABLE TIES TY-RAP® TY 27 MX 340X7.0 BK	0.236 in	3.543 in	0.276 in	13.386 in	black	500
61723060	CABLE TIES TY-RAP® TY 28 MX 361X4.8 BK	0.138 in	4.016 in	0.189 in	14.213 in	black	1,000
61723070	CABLE TIES TY-RAP® TY 29 MX 771X6.9 BK	0.236 in	9.016 in	0.272 in	30.354 in	black	500
61723110	CABLE TIES TY-RAP® TY 232 MX 203X2.3 BK	0.079 in	1.969 in	0.091 in	7.992 in	black	1,000
61723120	CABLE TIES TY-RAP® TY 234 MX 356X2.3 BK	0.079 in	4.016 in	0.091 in	14.016 in	black	1,000
61723130	CABLE TIES TY-RAP® TY 242 MX 208X3.6 BK	0.079 in	1.969 in	0.142 in	8.189 in	black	1,000
61723140	CABLE TIES TY-RAP® TY 244 MX 368X3.6 BK	0.079 in	4.055 in	0.142 in	14.488 in	black	1,000
61723150	CABLE TIES TY-RAP® TY 253 MX 290X4.8 BK	0.138 in	3.071 in	0.189 in	11.417 in	black	1,000
61723160	CABLE TIES TY-RAP® TY 272 MX 223X6.9 BK	0.236 in	1.969 in	0.272 in	8.78 in	black	500

V1.1