


END SLEEVES AHI-TWIN 2X1.50 BK

Article No.: 61802020

Conductor end sleeve; Suitable crimping insert: PEW 12.090-6; For cross-section: 1.5 mm²; black; Copper Tin-plated



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data
General information

Product type	Conductor end sleeve
Type of packaging	Cardboard packaging
Delivery Unit	500
Suitable crimping insert	PEW 12.090-6
Industry segment	Heating, Ventilation, Air Conditioning & Refrigeration

Electrical parameters
Product design

Conductor count/size	2
Total length	0.63 in
for cross-section	1.5 mm ²
Connector material	Copper
Insulation material	Polypropylene
Surface protection	Tin-plated
Colour description	black

Product features

Short term temperature max.	120 °C
Flame-retardant	No
UV-resistant	No
Chemical resistant	Yes
corrosion resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	No
EAC certified	Not required
EAC certification number	Отказное письмо № 39
UL recognized	No
UL listed	Yes
UL certification	according to UL 486F (CCN: ZMLF / e-file number: E507990)
UL category control number	ZMLF7
cUR recognized	No
cUL listed	Yes
cUL certification	according to CSA-C22.2 No. 291 (CCN: ZMLF7 / e-file number: E507990)
CSA certified	No
VDE certified	No

TWIN conductor end sleeves

Article No.	Name	Suitable crimping insert	for cross-section	Colour description	Delivery Unit
61801999	END SLEEVES AHI-TWIN 2X0.5 WH	PEW 12.090-6	0.5 mm ²	white	500
61802000	END SLEEVES AHI-TWIN 2X0.75 GY	PEW 12.090-6	0.75 mm ²	gray	500
61802010	END SLEEVES AHI-TWIN 2X1.00 RD	PEW 12.090-6	1 mm ²	red	500
61802020	END SLEEVES AHI-TWIN 2X1.50 BK	PEW 12.090-6	1.5 mm ²	black	500
61802030	END SLEEVES AHI-TWIN 2X2.50 BU	PEW 12.090-6	2.5 mm ²	blue	500
61802032	END SLEEVES AHI-TWIN 2X4.00 GY	PEW 12.090-6	4 mm ²	gray	100
61802033	END SLEEVES AHI-TWIN 2X6.00 YE	PEW 12.097	6 mm ²	yellow	100
61802034	END SLEEVES AHI-TWIN 2X10 RD	PEW 12.097	10 mm ²	red	100
61802035	END SLEEVES AHI-TWIN 2X16.0 N BU	PEW 12.097	16 mm ²	blue	50

V1.1