

**RING CABLE LUGS L-RA 35****Article No.:** 63104050

Cable lug; Suitable crimping insert: PEW 12.060; For cross-section (min./max.): 0.50mm<sup>2</sup> - 1.50mm<sup>2</sup>; red; Electrolytic copper Tin-plated

**Details****Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

**Remarks**

Trade product, not a LAPP product.

**Technical Data**
**General information**

|                          |                               |
|--------------------------|-------------------------------|
| Product type             | Cable lug                     |
| Type of packaging        | Bag                           |
| Delivery Unit            | 100                           |
| Suitable crimping insert | PEW 12.060                    |
| Industry segment         | Agricultural & Farm Machinery |

**Electrical parameters**

|                          |       |
|--------------------------|-------|
| applicable up to voltage | 400 V |
|--------------------------|-------|

**Product design**

|                          |                     |
|--------------------------|---------------------|
| Total length             | 0.689 in            |
| Screw hole size          | M3,5                |
| For cross-section (min.) | 0.5 mm <sup>2</sup> |
| For cross-section (max.) | 1.5 mm <sup>2</sup> |
| Connector material       | Electrolytic copper |
| Insulation material      | Polyamide           |
| Surface protection       | Tin-plated          |
| Colour description       | red                 |
| cable lug design         | Ring cable lug      |

**Product features**

|                               |           |
|-------------------------------|-----------|
| Flame-retardant               | Yes       |
| Flame retardance according to | UL 94 V-0 |
| UV-resistant                  | No        |
| Chemical resistant            | Yes       |
| corrosion resistant           | Yes       |

---

|               |     |
|---------------|-----|
| Halogenfree   | Yes |
| Oil resistant | Yes |

---

**Certifications and standards**

|                            |   |
|----------------------------|---|
| CE marking                 | No  |
| EAC certified              | Not required  |
| EAC certification number   | Отказное письмо № 39  |
| UL recognized              | No  |
| UL listed                  | Yes   |
| UL certification           | according to UL 486A/486B (e-file number: E334109)<br>according to UL 486C (e-file number: E334109)               |
| UL category control number | ZMVV7   |
| cUR recognized             | No  |
| cUL listed                 | Yes   |
| cUL certification          | according to CSA C22.2 No. 65 (e-file number: E334109)<br>according to CSA-C22.2 No. 188 (e-file number: E334109) |
| CSA certified              | No  |
| VDE certified              | No  |

---

**Ring cable lugs**

| Article No. | Name                    | Suitable crimping insert | For cross-section (min.) | For cross-section (max.) | Colour description | Delivery Unit |
|-------------|-------------------------|--------------------------|--------------------------|--------------------------|--------------------|---------------|
| 63104010    | RING CABLE LUGS L-RZ 3  | PEW 12.064               | 0.25 mm <sup>2</sup>     | 0.75 mm <sup>2</sup>     | green              | 100           |
| 63104020    | RING CABLE LUGS L-RZ 4  | PEW 12.064               | 0.25 mm <sup>2</sup>     | 0.75 mm <sup>2</sup>     | green              | 100           |
| 63104030    | RING CABLE LUGS L-RZ 5  | PEW 12.064               | 0.25 mm <sup>2</sup>     | 0.75 mm <sup>2</sup>     | green              | 100           |
| 63104040    | RING CABLE LUGS L-RA 3  | PEW 12.060               | 0.5 mm <sup>2</sup>      | 1.5 mm <sup>2</sup>      | red                | 100           |
| 63104050    | RING CABLE LUGS L-RA 35 | PEW 12.060               | 0.5 mm <sup>2</sup>      | 1.5 mm <sup>2</sup>      | red                | 100           |
| 63104060    | RING CABLE LUGS L-RA 4  | PEW 12.060               | 0.5 mm <sup>2</sup>      | 1.5 mm <sup>2</sup>      | red                | 100           |
| 63104070    | RING CABLE LUGS L-RA 5  | PEW 12.060               | 0.5 mm <sup>2</sup>      | 1.5 mm <sup>2</sup>      | red                | 100           |
| 63104080    | RING CABLE LUGS L-RA 6  | PEW 12.060               | 0.5 mm <sup>2</sup>      | 1.5 mm <sup>2</sup>      | red                | 100           |
| 63104160    | RING CABLE LUGS L-RB 3  | PEW 12.060               | 1.5 mm <sup>2</sup>      | 2.5 mm <sup>2</sup>      | blue               | 100           |
| 63104170    | RING CABLE LUGS L-RB 4  | PEW 12.060               | 1.5 mm <sup>2</sup>      | 2.5 mm <sup>2</sup>      | blue               | 100           |
| 63104180    | RING CABLE LUGS L-RB 5  | PEW 12.060               | 1.5 mm <sup>2</sup>      | 2.5 mm <sup>2</sup>      | blue               | 100           |
| 63104190    | RING CABLE LUGS L-RB 6  | PEW 12.060               | 1.5 mm <sup>2</sup>      | 2.5 mm <sup>2</sup>      | blue               | 100           |
| 63104200    | RING CABLE LUGS L-RB 8  | PEW 12.060               | 1.5 mm <sup>2</sup>      | 2.5 mm <sup>2</sup>      | blue               | 100           |
| 63104340    | RING CABLE LUGS L-RC 4  | PEW 12.060               | 4 mm <sup>2</sup>        | 6 mm <sup>2</sup>        | yellow             | 50            |
| 63104350    | RING CABLE LUGS L-RC 5  | PEW 12.060               | 4 mm <sup>2</sup>        | 6 mm <sup>2</sup>        | yellow             | 50            |
| 63104360    | RING CABLE LUGS L-RC 6  | PEW 12.060               | 4 mm <sup>2</sup>        | 6 mm <sup>2</sup>        | yellow             | 50            |
| 63104370    | RING CABLE LUGS L-RC 8  | PEW 12.060               | 4 mm <sup>2</sup>        | 6 mm <sup>2</sup>        | yellow             | 50            |
| 63104380    | RING CABLE LUGS L-RC 10 | PEW 12.060               | 4 mm <sup>2</sup>        | 6 mm <sup>2</sup>        | yellow             | 50            |

V1.1