

**EPIC® SOLAR 4 GEN2 M 5.2-7.0mm****Article No.:** 44428270`#{ctx.productData.top5String}`**Details****Benefits**

- Extremely weatherproof and durable thanks to the high-quality materials and solid construction.
- Compatible with other systems on the market.
- Ideal for fully automated plug connector assembly.
- Self-retaining cap nut and contacting with haptic feedback simplify assembly and provide protection from tampering.
- Double snap-in hooks secure the crimp contact to the connector.
- Low contact resistance at the contact point between plug and socket for efficient power supply.
- Suitable for conductor cross-sections up to 10 mm<sup>2</sup> for overcoming long cable distances.
- With the TÜV SÜD testing mark.
- Articles available in different packaging units.

**Application**

- For the cabling of solar modules, inverters and stand-alone systems.
- For modern, high-performance photovoltaic systems up to 1500 V.
- For use with EPIC® SOLAR 4 GEN2 F mating connectors (socket insert).
- Can be used with many ÖLFLEX® solar cables.
- Plugged connections have protection class IP 68 (1 m for 1 h).

### Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

### Remarks

### Technical Data

#### General information

Brand	EPIC®
Product type	Solar connector pin
Contacts included	No
Delivery Unit	100
Industry segment	Solar

#### Electrical parameters

Rated surge voltage	16 kV DC according to IEC 61984
Rated voltage	1500 V DC according to IEC
Rated current	50 A according to IEC

#### Product design

Contact variant	Pin
Connector housing design	Straight
Connector type	Plug
Min. cable clamping range	0.205 in
Cable clamping range max.	0.276 in
Housing main material	Polycarbonate
Housing base material, short form	PC
Colour description	black

**Product features**

IP protection rating mounted	IP 68 - 1m (1h)
Operating temperature max.	-40 °C
Operation temperature max.	85 °C
Flame-retardant	No
UV-resistant	Yes
Halogenfree	Yes

**Certifications and standards**

CE marking	Yes
UR recognized	No
CSA certified	No
VDE certified	No
TÜV certified	Yes
appliance class according to IEC 61140	II

**EPIC® SOLAR 4 GEN2 M**

Article No.	Name	Contacts included	Delivery Unit	Min. connectable conductor cross-section (mm <sup>2</sup> ) (in <sup>2</sup> )	Max. connectable conductor cross-section (mm <sup>2</sup> ) (in <sup>2</sup> )	Connectable conductor cross section min. (AWG)	Max. connectable conductor cross-section AWG	Min. cable clamping range	Cable clamping range max.	IP protection rating mounted	Connector housing design
381166461	EPIC® SOLAR 4 GEN2 M 5.2-7.0 mm	No	700					0.205 in	0.276 in	IP 68 - 1m (1h)	Straight
381166810	EPIC® SOLAR 4 GEN2 M 4-6 5.2-7.0mm	Yes	10	4 mm <sup>2</sup>	6 mm <sup>2</sup>	12 AWG	10 AWG	0.205 in	0.276 in	IP 68 - 1m (1h)	Straight
44428268	EPIC® SOLAR 4 GEN2 M 10mm <sup>2</sup>	Yes	100	10 mm <sup>2</sup>	10 mm <sup>2</sup>			0.276 in	0.291 in	IP 68 - 1m (1h)	Straight
44428270	EPIC® SOLAR 4 GEN2 M 5.2-7.0 mm	No	100					0.205 in	0.276 in	IP 68 - 1m (1h)	Straight
44428277	EPIC® SOLAR 4 GEN2 M 4-6 5.2-7.0mm	Yes	100	4 mm <sup>2</sup>	6 mm <sup>2</sup>	12 AWG	10 AWG	0.205 in	0.276 in	IP 68 - 1m (1h)	Straight

V1.1