

LS1.5 CRIMPTOOL 0,08-6,0**Article No.:** 44429367Crimping tool; For cross-section (min./max.): 0.08mm² - 6mm²;**Details****Benefits**

- With four simultaneously pressing mandrels for the highest crimping requirements.
- Digital display of the crimp dimension enables crimping accuracies of 0.01 mm.
- Crimp dimension can be displayed in mm, inches or in selector positions 1-8 according to MIL standard 22520.
- Current tool status can be called up at any time thanks to automatic wear calculation.
- Simple calibration option to avoid faulty crimp connections.

Application

- For making a secure crimp connection with turned contacts.
- For use with the circular connectors of the EPIC® POWER LS1.5 and EPIC® POWER LS3 series.

Notes

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Remarks

Technical Data

General information

Brand	EPIC®
Product type	Crimping tool
Delivery Unit	1

Electrical parameters**Product design**

For cross-section (min.)	0.08 mm ²
For cross-section (max.)	6 mm ²

Product features**Certifications and standards**

CE marking	No
VDE certified	No
TÜV certified	No

EPIC® POWER LS1.5 Tools

Article No.	Name	For cross-section (min.)	For cross-section (max.)	Crimping profile
44429367	LS1.5 CRIMPTOOL 0,08-6,0	0.08 mm ²	6 mm ²	
44429368	LS1.5 CRIMPTOOL 6,0-10,0			

V1.1