


PA-LOCKNUT M6X0,75 BK
Article No.: 51730210

\${ctx.productData.top5String}


Details
Benefits

- Available in sizes M6x0.75 and M8x1.0.

Application

- For locking a SKINDICHT® VENT pressure compensation element on the inside of the application (e.g. housing).
- For thin-walled housings without a thread, which only allow one through-hole.
- Good oil and chemical resistance.

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data

General information

Product type	Lock nut
Type of packaging	Bag
Delivery Unit	25

Electrical parameters

Product design

Glass-fibre reinforced	No
Thread type	Metric
Thread size	M 6
Pitch of thread	0,75
Thread length	0.197 in
Wrench width	0.394 in
EMC shielding	No
Body material	Polyamide
Body material, short form	PA
Surface protection	Uncoated
Colour description	black
RAL color	RAL 9005

Product features

Suitable for EX-applications	No
Temperature (min.)	-40 °C
Max. temperatur	100 °C
Flame-retardant	No
UV-resistant	Yes
Halogenfree	No

Oil resistant	Yes
Impact proof	No

Certifications and standards

CE marking	No
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

Locknuts PA

Article No.	Name	Thread size	Wrench width	Colour description	Delivery Unit
51730210	PA-LOCKNUT M6X0,75 BK	M 6	0.394 in	black	25
51730211	PA-LOCKNUT M6X0,75 LGY	M 6	0.472 in	light gray	25
51730213	PA-LOCKNUT M8X1,0 BK	M 8	0.394 in	black	25
51730214	PA-LOCKNUT M8X1,0 LGY	M 8	0.472 in	light gray	25

V1.1