

SKINTOP® HYGIENIC M32X1.5
Article No.: 53105140

Cable gland; M 32; Clamping range (min./max.): 0.63 - 0.787 in; Wrench width 1: 1.417; Stainless steel Uncoated; UV-resistant; IP 68 - 10 g/cm² (30 min), IP 69;


Details
Benefits

- Hygienic design with smooth surfaces and contours without corners and edges prevents residues such as liquids and micro-organisms from accumulating and posing a risk of contamination for food processing machinery. This facilitates simple, frequent and safe product cleaning.
- Multiple food and beverage certifications for Europe and North America.
- Tested resistance to ECOLAB® disinfectants and cleaning agents.
- The best possible sealing enables protection classes IP 68 (10 bar) and IP 69.
- Sealing material in blue to easily distinguish the cable glands used in the food industry.
- Sealing material compliant with FDA 21 CFR 177.2600, specifically for the food and beverage industry in North America.

-
- Certified according to NSF/ANSI 169 for use in hygiene-critical areas in North America (Standard: Special Purpose Food Equipment and Devices/for Use in Food Zone Non Contact).

Application

- For sealing and strain relieving cable insertion into a housing.
- Especially for hygiene-critical areas of the food industry, where the product needs to be installed in the product zone or in the direct food production environment.
- Also suitable for use in hygiene-critical areas of the pharmaceutical and chemical industry.
- Withstands high chemical and mechanical loads.
- Suitable for applications with UV-C radiation (according to LAPP's internal test method).

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks**Technical Data****General information**

Brand	SKINTOP®
Product type	Cable gland
Delivery with lock nut	No
Type of packaging	Bag
Delivery Unit	5
Industry segment	Food & Beverage Healthcare & Pharma

Electrical parameters

Product design

For armored cables	No
Glass-fibre reinforced	No
Number of cable entries	1 pc.
With bending protection	No
Cable gland design	Straight
Total length	2.205 in
Clear width	0.787 in
Thread type	Metric
Thread size	M 32
Pitch of thread	1,5
Thread length	0.354 in
Thread standard	DIN EN 60423
Spanner size 1	1.417 in
Wrench size 2	1.417 in
Hexagon corner dimensions	1.559 in
Clamping range min.	0.63 in
Clamping range max.	0.787 in
EMC shielding	No
Material insert	Polyamide
Seal type	Conduit Sealing Ring
Thread-side sealing element	Flat seal
Cable-side sealing element	Conduit Sealing Ring
Material sealing	Fluorinated rubber
Body material	Stainless steel
Body material, short form	V4A
Surface protection	Uncoated
Colour description	metal

Product features

IP protection rating	IP 68 - 10 g/cm ² (30 min) IP 69
----------------------	--

NEMA classification type	Type 1 Type 2 Type 4x Type 6 Type 12
Suitable for EX-applications	No
Temperature (min.)	-20 °C
Max. temperatur	100 °C
Flame-retardant	Yes
UV-resistant	Yes
UV-C resistant	Yes
Chemical resistant	Yes
Acid-resistant	Yes
corrosion resistant	Yes
Halogenfree	No
Oil resistant	Yes
Impact proof	Yes
Vibration protection	Yes
Strain relief	Yes

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
For Ex zone gas	without
For Ex-zone dust	without
GGVS certified	No
DNV-certified	No
Tested for fire protection for railway vehicles	No
Ecolab certified	Yes

NSF certified	Yes
FDA certified	Yes
FDA certification according to	CFR 21
EHEDG certified	Yes

SKINTOP® HYGIENIC / SKINTOP® HYGIENIC-R

Article No.	Name	Thread size	Thread length	Clamping range min.	Clamping range max.	Spanner size 1	Delivery Unit
53105100	SKINTOP® HYGIENIC M12X1.5	M 12	0.256 in	0.157 in	0.236 in	0.63 in	5
53105110	SKINTOP® HYGIENIC M16X1.5	M 16	0.276 in	0.256 in	0.354 in	0.787 in	5
53105120	SKINTOP® HYGIENIC M20X1.5	M 20	0.315 in	0.354 in	0.472 in	0.945 in	5
53105130	SKINTOP® HYGIENIC M25X1.5	M 25	0.315 in	0.453 in	0.61 in	1.142 in	5
53105140	SKINTOP® HYGIENIC M32X1.5	M 32	0.354 in	0.63 in	0.787 in	1.417 in	5
53105141	SKINTOP® HYGIENIC M40X1.5	M 40	0.354 in	0.866 in	1.063 in	1.772 in	5
53105200	SKINTOP® HYGIENIC-R M12X1.5	M 12	0.256 in	0.118 in	0.177 in	0.63 in	5
53105210	SKINTOP® HYGIENIC-R M16X1.5	M 16	0.276 in	0.177 in	0.276 in	0.787 in	5
53105220	SKINTOP® HYGIENIC-R M20X1.5	M 20	0.315 in	0.276 in	0.394 in	0.945 in	5
53105230	SKINTOP® HYGIENIC-R M25X1.5	M 25	0.315 in	0.354 in	0.492 in	1.142 in	5
53105240	SKINTOP® HYGIENIC-R M32X1.5	M 32	0.354 in	0.492 in	0.65 in	1.417 in	5

V1.1