

**CRIMPING PLIERS DKB 0325****Article No.:** 61722110

Crimping tool; For cross-section (min./max.): 0.35mm<sup>2</sup> - 2.50mm<sup>2</sup>; Crimping profile:  
Mandrel Pressing

**Details****Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

**Remarks**

Trade product, not a LAPP product.

**Technical Data****General information**

Product type	Crimping tool
Delivery Unit	1

---

**Electrical parameters****Product design**

For pressing	Non-insulated cable lug Tube cable lug KR
Total length	7.559 in
For cross-section (min.)	0.35 mm <sup>2</sup>
For cross-section (max.)	2.5 mm <sup>2</sup>
Colour description	orange/black
Crimping profile	Mandrel Pressing

**Product features**

Number of application operations	80,000
----------------------------------	--------

**Certifications and standards**

CE marking	No
VDE certified	No
TÜV certified	No

---

**DKB 0325 + DKB 0360 crimping pliers**

Article No.	Name	For cross-section (min.)	For cross-section (max.)	Crimping profile
61722110	CRIMPING PLIERS DKB 0325	0.35 mm <sup>2</sup>	2.5 mm <sup>2</sup>	Mandrel Pressing
61790920	CRIMPING PLIERS DKB 0360	0.35 mm <sup>2</sup>	6 mm <sup>2</sup>	Mandrel Pressing
61790930	CRIMPING PLIERS DRB 0505	0.05 mm <sup>2</sup>	0.5 mm <sup>2</sup>	Roller Pressing
61790940	CRIMPING PLIERS DRB 0115	0.1 mm <sup>2</sup>	1.5 mm <sup>2</sup>	Roller Pressing

V1.1