

CRIMPING PLIERS HYDRAULIC V 1311
Article No.: 61795925

 Hydraulic crimping tool; For cross-section (min./max.): 10mm² - 400mm²;


Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data

General information

Product type	Hydraulic crimping tool
Scope of delivery	without crimping inserts
Delivery Unit	1

Electrical parameters**Product design**

For pressing	Tube cable lug
Total length	23.228 in
For cross-section (min.)	10 mm ²
For cross-section (max.)	400 mm ²

Product features

Pressing force	130 kN
----------------	--------

Certifications and standards

CE marking	Yes
VDE certified	No
TÜV certified	No

V 1311-A pressing pliers, hydraulic

Article No.	Name	For cross-section (min.)	For cross-section (max.)	Crimping profile
61795925	CRIMPING PLIERS HYDRAULIC V 1311	10 mm ²	400 mm ²	

V1.1