

**CRIMPING PLIERS PEW 8.87**

**Article No.:** 61813742

Crimping tool; For cross-section (min./max.): 0.08mm<sup>2</sup> - 10mm<sup>2</sup>; Crimping profile: Square



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

**Remarks**

Trade product, not a LAPP product.

**Technical Data**

**General information**

Product type	Crimping tool
Delivery Unit	1

---

**Electrical parameters****Product design**

For pressing	Insulated conductor end sleeves Non-insulated conductor end sleeves
Total length	7.48 in
For cross-section (min.)	0.08 mm <sup>2</sup>
For cross-section (max.)	10 mm <sup>2</sup>
Material	Steel
Surface protection	Burnished
Colour description	orange
Crimping profile	Square

**Product features**

corrosion resistant	Yes
---------------------	-----

**Certifications and standards**

CE marking	No
VDE certified	No
TÜV certified	No

---

**PEW 8.87 crimping pliers**

Article No.	Name	For cross-section (min.)	For cross-section (max.)	Crimping profile
61813742	CRIMPING PLIERS PEW 8.87	0.08 mm <sup>2</sup>	10 mm <sup>2</sup>	Square
61813744	CRIMPING PLIERS PEW 8.87 PLUS	0.08 mm <sup>2</sup>	16 mm <sup>2</sup>	Square

V1.1