

CRIMPING INSERT PEW 12.020

Article No.: 61813823

Crimping insert; For cross-section (min./max.): 0.5mm² - 2.5mm²; Crimping profile: Mandrel Pressing; For crimping tool: PEW 12



Details

Notes

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data

General information

Product type	Crimping insert
Scope of delivery	without crimping tool
Delivery Unit	1
for crimping tool	PEW 12

Electrical parameters**Product design**

For cross-section (min.)	0.5 mm ²
For cross-section (max.)	2.5 mm ²
Crimping profile	Mandrel Pressing

Product features**Certifications and standards**

Crimping inserts for PEW 12 system

Article No.	Name	For cross-section (min.)	For cross-section (max.)	for cross-section	Crimping profile	for crimping tool
61813802	CRIMPING INSERT PEW 12.090	0.25 mm ²	6 mm ²		Trapezoid	PEW 12,E-PEW 12,CM 25-1
61813803	CRIMPING INSERT PEW 12.091	10 mm ²	25 mm ²		W pressing	PEW 12,E-PEW 12,CM 25-1
61813808	CRIMPING INSERT PEW 12.050	0.5 mm ²	6 mm ²		Roller Pressing	PEW 12,E-PEW 12,CM 25-1
61813809	LOCATOR PEW 12.050-014	1 mm ²	2.5 mm ²			PEW 12,E-PEW 12,CM 25-1
61813812	CRIMPING INSERT PEW 12.060	0.5 mm ²	6 mm ²		Conical ISO Crimp	PEW 12,E-PEW 12,CM 25-1
61813823	CRIMPING INSERT PEW 12.020	0.5 mm ²	2.5 mm ²		Mandrel Pressing	PEW 12
61813862	CRIMPING INSERT PEW 12.033	16 mm ²	25 mm ²		Mandrel Pressing	PEW 12,E-PEW 12,CM 25-1
61813911	CRIMPING INSERT PEW 12S.093			70 mm ²	W pressing	PEW 12S,E-PEW 12
61813912	CRIMPING INSERT PEW 12S.094			95 mm ²	W pressing	PEW 12S,E-PEW 12
61813913	CRIMPING INSERT PEW 12.090-6	0.5 mm ²	4 mm ²		Trapezoid	PEW 12,E-PEW 12,CM 25-1
61813914	CRIMPING INSERT PEW 12.064	0.14 mm ²	1 mm ²		Conical ISO Crimp	PEW 12,E-PEW 12
61813916	CRIMPING INSERT PEW 12.1071	0.5 mm ²	10 mm ²		W pressing	PEW 12,E-PEW 12,CM 25-1
61813991	CRIMPING INSERT PEW 12.838	0.5 mm ²	1.5 mm ²		Roller Pressing	PEW 12,E-PEW 12,CM 25-1
61813992	LOCATOR PEW 12.838	0.75 mm ²	1.5 mm ²			PEW 12,E-PEW 12,CM 25-1
61813993	CRIMPING INSERT PEW 12.331	35 mm ²	50 mm ²		W pressing	PEW 12,E-PEW 12
61814600	CRIMPING INSERT PEW 12.045	0.1 mm ²	2.5 mm ²		Roller Pressing	PEW 12,E-PEW 12,CM 25-1
61814601	LOCATOR PEW 12.045	0.1 mm ²	2.5 mm ²			PEW 12,E-PEW 12,CM 25-1
61815642	CRIMPING INSERT PEW 12.097	6 mm ²	16 mm ²		W pressing	PEW 12,E-PEW 12,CM 25-1
61815643	CRIMPING INSERT PEW 12.751	4 mm ²	6 mm ²		Roller Pressing	PEW 12,E-PEW 12,CM 25-1
61815644	LOCATOR PEW 12.751	4 mm ²	6 mm ²			PEW 12,E-PEW 12,CM 25-1
61815645	CRIMPING INSERT PEW 12.465	1 mm ²	2.5 mm ²		Roller Pressing	PEW 12,E-PEW 12,CM 25-1
61815646	LOCATOR PEW 12.465	1.5 mm ²	2.5 mm ²			PEW 12,E-PEW 12,CM 25-1

V1.1