

END JOINT L-RCJ**Article No.:** 63112020

Cable lug; Suitable crimping insert: PEW 12.060; For cross-section (min./max.): 4mm² - 6mm²; transparent;

**CE****Details****Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data
General information

Product type	Cable lug
Type of packaging	Bag
Delivery Unit	50
Suitable crimping insert	PEW 12.060

Electrical parameters
Product design

For cross-section (min.)	4 mm ²
For cross-section (max.)	6 mm ²
Connector material	Electrolytic copper
Insulation material	Polyamide
Colour description	transparent
cable lug design	End connector

Product features

Short term temperature max.	120 °C
Flame-retardant	No
UV-resistant	No
Chemical resistant	Yes
corrosion resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	Yes
------------	-----

EAC certified	Not required
EAC certification number	Отказное письмо № 39
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No

End joint

Article No.	Name	Suitable crimping insert	For cross-section (min.)	For cross-section (max.)	Colour description	Delivery Unit
63112010	END JOINT L-RBJ	PEW 12.060	1.5 mm ²	2.5 mm ²	transparent	100
63112020	END JOINT L-RCJ	PEW 12.060	4 mm ²	6 mm ²	transparent	50

V1.1